

USB 3.0 to HDMI Adapter - 1080p (1920x1200) - Slim/Compact USB Type-A to HDMI Display Adapter Converter for Monitor - External Video & Graphics Card - Black - Windows Only - TAA

Product ID: USB32HDES



The USB32HDES Slim USB 3.0 to HDMI Adapter turns a USB 3.0 port into an HDMI output with 1920x1200/1080p video support. The adapter minimizes clutter with a slim design that seamlessly blends with your video cable - an ideal space-saving solution for multi-monitor applications on Ultrabook, laptop, or desktop computers.

Functioning as an external graphics card, this USB to HDMI adapter provides a convenient way to add multi-monitor capability to a USB 3.0-enabled desktop or laptop computer (optimal performance from USB 3.0, backward compatible with USB 2.0).

To save space while travelling, this ultra-portable USB to HDMI adapter features a lightweight, small footprint design that fits easily in a laptop carrying bag.

Leveraging the high-bandwidth (5 Gbps) SuperSpeed USB 3.0 interface, the adapter delivers smooth, high-definition content to your HDMI display/projector. The adapter can be used to mirror your primary desktop, showing the same image on each display, or to extend your desktop to double your workspace and increase your productivity.

The USB32HDES is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Recommended System Requirements:

CPU: Quad Core 2.4GHz or Higher (i5 recommended)

RAM: 4GB or higher

USB 3.0 Port (Backwards compatible with USB 2.0)

Certifications, Reports and Compatibility



Applications

- Add a secondary HDMI display with full HD capability
- View large or multiple spreadsheets across several displays
- Use the adapter to connect your PC to your HDMI-equipped projector or display for viewing family pictures and movies
- Add multi-monitor capability to a single computer, to create engaging multimedia presentations
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other
- Run multiple applications on different screens - check your email on one display and search the web on the other

Features

- **PERFORMANCE:** USB 3.0 to HDMI adapter lets you connect your laptop or desktop computer to an HDMI monitor or projector using a single USB Type-A port; 1920x1200 (1080p) Video; 2ch audio (through HDMI); 2.4in (6cm) cable length
- **INCREASE PRODUCTIVITY:** Supports a total of 2 displays in extended mode (incl. laptop screen) at your workstation or working remotely from home; USB bus-powered w/ no extra power supply required; Ultra slim design and highly portable
- **WINDOWS ONLY:** This USB-A to HDMI monitor adapter is only compatible with Windows operating systems and does not support macOS, Chrome or Linux; External USB 3.0 (USB 3.1 Gen 1) Graphics Card Adapter for dual/multiple monitors
- **EASY SETUP:** USB to HDMI converter with plug & play setup on Windows; Auto-driver install (administrator rights required); Slim design with a seamless connection to your HDMI cable; Add multiple HDMI screens with additional available USB-A ports
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this USB Type-A to HDMI adapter dongle is backed for 3-years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty

3 Years

AV Input	USB 3.2 Gen 1 (5Gbps)
AV Output	HDMI
Audio	Yes
USB Pass-Through	No
Memory	16MB
Chipset ID	Trigger - T5-302

Performance

Maximum Digital Resolutions	1920x1200/1080p
Supported Resolutions	Widescreen(16/32 bit): 1920x1200, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720 Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
Wide Screen Supported	Yes
Audio Specifications	2-Channel Stereo (48Khz)

Connector(s)

Connector A	1 - USB Type-A (9 pin, 5 Gbps)
Connector B	1 - HDMI (19 pin)

Software

OS Compatibility	Windows 11 Windows 10 (32/64) Windows 8 / 8.1 (32/64) Windows 7(32/64) Windows Vista (32/64) Windows XP (32/64)
Microsoft WHQL Certified	Yes

Special Notes / Requirements

System and Cable Requirements	System Processor: Quad Core 2.4GHz (i5 recommended) System Memory: 4GB
Note	Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources This USB video adapter is not intended for graphical intensive applications, such as gaming

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-10C to 75C (14F to 167F)
Humidity	< 85% non-condensing

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	2.4 in [62 mm]
Product Length	7.5 in [19.0 cm]
Product Width	1.0 in [2.5 cm]
Product Height	0.5 in [1.2 cm]
Weight of Product	0.9 oz [25.0 g]

Packaging Information

Package Quantity	1
Package Length	6.8 in [17.2 cm]
Package Width	5.7 in [14.6 cm]
Package Height	1.3 in [3.2 cm]
Shipping (Package)	5.2 oz [146.0 g]

Weight

What's in the Box

Included in Package	1 - Slim USB 3.0 Video Adapter
	1 - Driver CD
	1 - instruction manual

**Product appearance and specifications are subject to change without notice.*