

## USB 3.0 to HDMI Adapter - DisplayLink Certified - 1920x1200

Product ID: USB32HDPRO



The USB32HDPRO USB 3.0 to HDMI Adapter lets you add an HDMI display to your computer through a USB 3.0 port, providing a cost-effective and convenient way to expand the video capabilities of your Mac or PC computer system.

With USB 3.0 support, this external video adapter delivers the bandwidth needed for accelerated High-Definition video performance, capable of outputting video resolutions up to 1920x1200 / 1080p. Even if your current computer doesn't have a USB 3.0 port available, the USB32HDPRO is backward compatible with USB 2.0, so you'll be able to connect your HDMI monitor to your computer and be ready for when you upgrade to a USB 3.0-equipped system.

Add the screen space you need to simplify multitasking and maximize productivity, without even opening your computer case. Some computer systems, including MacBook and Ultrabook laptops and small form-factor desktops, are too compact to install an internal video card. A USB display adapter offers an easy workaround, performing as an external video card that only requires an available USB port to mirror or extend your desktop onto another display.

Installation has never been easier. When you connect this DisplayLink Plug and Display certified adapter to a web-enabled Windows 10, Windows 8 or Windows 7 computer, it automatically downloads and installs the most up-to-date drivers for you, so you won't have to manually download or install any software.

The USB32HDPRO is backed by a StarTech.com 2-year warranty and free lifetime technical support.

<br />CPU: Quad Core 2.4GHz or Higher (i5 recommended)<br />RAM: 4GB or higher

### Certifications, Reports and Compatibility





## Applications

- Add a secondary DisplayPort display and extend your desktop, without taking apart your computer to install a new video card
- Add multi-monitor capability to a single computer, to enhance multimedia presentations
- Great for researchers and writers, offering the ability to have reference material on one display while working on a separate document on another
- Increase productivity by running multiple applications on different screens - check your email on one display and search the web on the other
- View large or several spreadsheets across multiple displays
- A compact, lightweight solution for traveling business associates using USB 3.0-capable laptop PCs, enabling connection to a secondary display/projector
- Add an additional video output to computer systems with no room for expansion, such as laptops, ultrabooks, MacBooks, and compact form factor desktops (point of sale workstations)

## Features

- Works with Mac & PC
- USB 3.0 host connection provides maximum bandwidth for superior performance
- DisplayLink Plug-and-Display certified - automatic driver installation and updates
- USB-powered - No external power adapter required
- Supports 5.1 channel audio
- Supports video resolutions up to 1920x1200 / 1080p
- Backward compatible with USB 2.0
- Increase productivity by mirroring or extending your desktop onto another display

|                    |                             |   |
|--------------------|-----------------------------|---|
| <b>Hardware</b>    | Warranty                    | 2 Years   |
|                    | AV Input                    | USB 3.0   |
|                    | AV Output                   | HDMI  |
|                    | Audio                       | Yes   |
|                    | USB Pass-Through            | No  |
|                    | Memory                      | 512MB   |
|                    | Chipset ID                  | DisplayLink - DL-3500   |
| <b>Performance</b> | Maximum Digital Resolutions | 1920x1200 / 1080p   |
|                    | Supported Resolutions       | Widescreen(16/32 bit):  |
|                    | Wide Screen Supported       | 1920x1200, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720 |
|                    | Audio Specifications        |   |

|                        |  |
|------------------------|--|
| General Specifications | Standard(16/32 bit):   |
| General Specifications | 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600   |
| MTBF                   | Yes  |
|                        | 5.1-Channel Surround (48Khz)   |
|                        | If using OS X 10.8, Apple update 10.8.3 must be installed before installing DisplayLink software. 10.8.3 fixes several serious OS X bugs exposed when DisplayLink software is installed.   |
|                        | This USB video adapter uses a DisplayLink family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a Trigger or Fresco family chipset. |
|                        | 87,880 hours   |

---

|                     |             |                                     |
|---------------------|-------------|-------------------------------------|
| <b>Connector(s)</b> | Connector A | USB Type-A (9 pin) USB 3.0 (5 Gbps) |
|                     | Connector B | HDMI (19 pin)                       |

---

|                 |                  |  |
|-----------------|------------------|--|
| <b>Software</b> | OS Compatibility | Windows 2000, XP, Vista, 7, 8, 8.1, 10 |
|                 |                  | macOS 10.6 - 10.12, 10.14 - 10.15      |
|                 |                  | Ubuntu 14.04, 16.04, 18.04             |
|                 |                  | Chrome OS v55+                         |

---

|                                     |                               |  |
|-------------------------------------|-------------------------------|--|
| <b>Special Notes / Requirements</b> | System and Cable Requirements | System Processor: Quad Core 2.4GHz (i5 recommended)  |
|                                     | Note                          | System Memory: 4GB   |
|                                     | Note                          | This USB video adapter uses a DisplayLink family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as Trigger or Fresco Logic |
|                                     | Note                          | Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources  |
|                                     |                               | This USB video adapter is not intended for graphical intensive applications, such as gaming  |


---

|              |              |             |
|--------------|--------------|-------------|
| <b>Power</b> | Power Source | USB-Powered |
|--------------|--------------|-------------|

---

|                      |                       |                          |
|----------------------|-----------------------|--------------------------|
| <b>Environmental</b> | Operating Temperature | 0C to 35C (32F to 95F)   |
|                      | Storage Temperature   | -5C to 40C (23F to 104F) |
|                      | Humidity              | 20C to 80C (68F to 176F) |

---



|                                 |                           |                            |
|---------------------------------|---------------------------|----------------------------|
| <b>Physical Characteristics</b> | Color                     | Black                      |
|                                 | Material                  | Plastic                    |
|                                 | Cable Length              | 36.0 in [9.1 cm]           |
|                                 | Product Length            | 3.5 in [90 mm]             |
|                                 | Product Width             | 2.2 in [55 mm]             |
|                                 | Product Height            | 0.8 in [20 mm]             |
|                                 | Weight of Product         | 2.2 oz [62 g]              |
| <hr/>                           |                           |                            |
| <b>Packaging Information</b>    | Package Length            | 8.3 in [2.1 cm]            |
|                                 | Package Width             | 5.7 in [1.4 cm]            |
|                                 | Package Height            | 1.6 in [40 mm]             |
|                                 | Shipping (Package) Weight | 6.9 oz [196 g]             |
| <hr/>                           |                           |                            |
| <b>What's in the Box</b>        | Included in Package       | USB 3.0 to HDMI Adapter    |
|                                 | Included in Package       | Software installation disc |
|                                 | Included in Package       | Instruction Manual         |
| <hr/>                           |                           |                            |

***\*Product appearance and specifications are subject to change without notice.***

