

## 3m USB 3.0 Active Extension Cable - M/F

Produkt ID: USB3AAEXT3M



The USB3AAEXT3M, 3-meter Active USB 3.0 Extension Cable, offers one USB type-A (male) connector and one USB type-A (female) connector, and provides an active extension of USB 3.0 devices of up to 3-meters (10-feet).

An all-in-one cable for overcoming distance restrictions as well as power source limitations; the active USB 3.0 extension cable incorporates bus-powered active circuitry to ensure performance beyond the typical length limits of standard USB cables. Up to 4 of these cables can be daisy-chained together, allowing the connection to be extended a total of 12-meters. If necessary, the USB device can be powered from a wall outlet, using the Universal AC power adapter provided with the cable.

The USB3AAEXT3M extension cable (USB Extender) supports high speed USB 3.0 transfer rates of up to 5Gbps, and is backed by StarTech.com's 2-year Warranty.

## Certifikat, rapporter och kompatibilitet

### Användning

- Extend the distance of USB peripherals beyond the USB 3.0 3-meter limitation
- Cascade up to 4 levels
- Backwards compatible with USB 2.0/1.1 devices

### Funktioner

- Fully shielded for error-free connections
- Plug-and-play, no driver required
- USB bus-powered
- Universal external power source also included
- Blue LED indicator x1 for Extension Cable and USB port connection status monitoring
- Compatible with PC Windows® 8/7/Vista/XP and Mac computer systems

---

#### Hårdvara

Garantipolicy	2 Years
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride

---

#### Kontakt(er)

Connector A	USB Type-A (9-stifts) USB 3.0 (5 Gbps)
Connector B	USB Type-A (9-stifts) USB 3.0 (5 Gbps)

---

#### Särskilda anmärkningar/krav

Obs.	Cascade up to 4 USB3AAEXT3M devices together for further extension
------	--

---

#### Ström

Power Source	AC-adapter medföljer
Inspänning	100 - 240 AC
Inström	0.35 A
Utspänning	5 DC
Utström	2A
Polaritet på mittpol	Positiv
Kontakttyp	H
Strömförbrukning	10

---

Utseende

Färg	Svart
Kabellängd	9.8 ft [3 m]
Produktlängd	9.8 ft [3.0 m]
Produktbredd	0.0 in [0.0 mm]
Produkt höjd	0.0 in [0.0 mm]
Produktvikt	8.1 oz [230.0 g]

---

Förpackning

Förpackningsantal	1
Package Length	9.3 in [23.5 cm]
Package Width	5.8 in [14.8 cm]
Package Height	2.0 in [52.0 mm]
Fraktvikt (förpackning)	10.8 oz [305.0 g]

---

Vad det är i lådan

Ingår i paketet	3 m USB 3.0 Active Extension Cable - M/F
	Universal Power Adapter
	Plug Adapters for North America, UK, Europe, and Australia

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

