

## Slim Micro-USB 3.0 Cable - M/M - Left-Angle Micro USB - 2m (6ft)

Product ID: USB3AU2MLS



This slim, sturdy USB 3.1 Gen 1 (5 Gbps) cable, better known as a USB 3.0 cable, lets you position Micro-USB devices on your desk without the cable getting in the way. It's thinner and more flexible than standard cables, and features a left-angled Micro-USB connector that prevents awkward bends at the connection port.

Now you can arrange your desk according to what works best for you, without worrying about the cable bending awkwardly or straining too much to make a connection. This durable, lightweight cable is roughly half the thickness of a regular USB 3.0 cable, giving you the flexibility and freedom to place your devices as needed, with minimal clutter.

This versatile cable features a left-angled connector, which offers a more natural fit at the device connection point, preventing unnecessary strain and damage to the port.

Charge your USB 3.0 Micro B-equipped phones and tablets with full charging power, with no increase in charge time, even at a distance of 6 feet (2 meters) away from your charger.

The long cable overcomes distance restrictions and lets you stay connected even while you're taking notes in a boardroom, catching up on emails in a hotel room, or reading in a coffee shop.

The cable features a thin, yet sturdy connector molding, so you'll be able to connect to your phone or tablet without removing its protective case. Plus, the cable's left-angled Micro-USB connector lets you text, work or game on your mobile device even while it's charging, without the cable getting in the way.

The USB3AU2MLS 2-meter is backed by StarTech.com's lifetime warranty for guaranteed reliability.

## Certifications, Reports and Compatibility



## Applications

- Connect Micro-USB 3.0 devices (portable hard drive, card reader, video capture device, hard drive enclosure, etc.) to a USB 3.0 compatible PC or laptop
- Charge and sync your USB 3.0 Micro B-equipped mobile digital devices

## Features

- Position your USB 3.0 devices as needed throughout your workspace
- Connect to your device even in hard to reach areas and tight spaces
- Charge and sync your mobile devices without removing the protective case

<b>Hardware</b>	Warranty	90 Days
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
<b>Performance</b>	Type and Rate	USB 3.0 - 5 Gbit/s
<b>Connector(s)</b>	Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
	Connector B	USB 3.0 Micro-B (10 pin, SuperSpeed)
<b>Physical Characteristics</b>	Color	Black
	Connector Style	Straight to Left Angle
	Wire Gauge	26/32 AWG
	Cable Length	6.6 ft [2 m]
	Product Length	6.6 ft [2 m]
	Weight of Product	0.0 oz [0.105 g]
<b>Packaging Information</b>	Package Quantity	1
	Package Length	8.9 in [2.2 cm]
	Package Width	4.9 in [1.2 cm]
	Package Height	0.8 in [20 mm]
	Shipping (Package) Weight	3.7 oz [106 g]
<b>What's in the Box</b>	Included in Package	2m Left-Angle Slim Micro-USB 3.0 Cable

*\*Product appearance and specifications are subject to change without notice.*