

Slim Micro USB 3.0 (5Gbps) Cable - M/M - 1m (3ft)

Product ID: USB3AUB1MS



Does your regular USB 3.2 Gen 1 cable lift or push against your external hard drive causing it to move around on your desk? Are you forced to arrange your desk according to how your cable decides to bend and rest?

The USB3AUB1MS features a slim USB wire construction that makes it easier to install your USB 3.2 Gen 1 devices and enables you to place them as needed throughout your workspace. Plus, the thin Micro USB connector molding makes this a great cable for mobile USB 3.2 Gen 1 devices too - it lets you plug into your device without having to take it out of its case for every charge and sync.

Organize your desk and your office to match your needs. This durable, lightweight cable is approximately half the thickness of a regular USB 3.2 Gen 1 cable giving you the freedom to place your devices as needed and with minimal clutter. The flexible, thin cable also reduces strain on the connection and prevents damage to the USB 3.2 Gen 1 port on your device.

Replace the cable that came with your Micro USB mobile device or keep one as a spare while traveling.

As well as being ideal for connecting to your desktop devices, this cable provides the perfect solution for charging and syncing your USB 3.2 Gen 1 Micro B-equipped phones and tablets.

Stop removing the case from your phone or tablet every time you charge or sync your device. The cable offers a thin Micro USB connector molding that plugs into your device even while it's inside a protective case.

This 1-meter Micro USB 3.2 Gen 1 cable is backed by StarTech.com's Lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Connect Micro USB 3.0 devices (portable hard drive, card reader, video capture device, hard drive enclosure, etc.) to a USB 3.0 compatible PC or laptop
- Charge and sync your USB 3.0 Micro B-equipped mobile digital devices

Features

- Slim cable construction – outer diameter (OD) of 4.8mm
- Redesigned, thin Micro USB 3.2 Gen1 connector molding
- Supports USB 3.2 Gen1 data transfer rates up to 5Gbps
- Cable and connectors are compliant with USB 3.2 Gen1 SuperSpeed specifications
- Aluminum-Mylar Foil with Braided Shielding
- Molded connectors with strain relief

Hardware

| | |
|-----------------------|--------------------------------|
| Warranty | Lifetime |
| Connector Plating | Nickel |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

Performance

| | |
|---------------|--------------------|
| Type and Rate | USB 3.0 - 5 Gbit/s |
|---------------|--------------------|

Connector(s)

| | |
|-------------|--|
| Connector A | 1 - USB Type-A (9 pin, 5 Gbps) |
| Connector B | 1 - USB 3.0 Micro-B (10 pin, SuperSpeed) |

Physical Characteristics

| | |
|-----------------|-----------|
| Color | Black |
| Connector Style | Straight |
| Wire Gauge | 26/32 AWG |

| | |
|-------------------|----------------|
| Cable Length | 3.3 ft [1 m] |
| Product Length | 3.3 ft [1 m] |
| Weight of Product | 0.0 oz [0.1 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Quantity | 1 |
| Package Length | 8.9 in [22.5 cm] |
| Package Width | 4.8 in [12.3 cm] |
| Package Height | 2.0 in [50 mm] |
| Shipping (Package) Weight | 2.3 oz [65 g] |

What's in the Box

| | |
|---------------------|---|
| Included in Package | 1 - 1m (3ft) Slim SuperSpeed USB 3.0 A to Micro B Cable - M/M |
|---------------------|---|

****Product appearance and specifications are subject to change without notice.***