

3 ft SuperSpeed USB 3.0 to eSATA Cable Adapter

Product ID: USB3S2ESATA



The USB3S2ESATA USB 3.0 to eSATA Adapter Cable lets you connect an external SATA (eSATA) device or enclosure to a host computer through USB 3.0, in a single convenient package. The adapter cable combines USB 3.0 and eSATA cables into an integrated cable, with no external power adapter or driver installation required, for simple and hassle-free installation - No assembly or searching for the right cable required.

With support for SuperSpeed USB 3.0 connectivity at transfer rates up to 5 Gbps (10 times faster than USB 2.0), and backward compatibility with USB 2.0, the USB 3.0 to eSATA adapter cable provides a fast and easy-to-use Plug-and-Play experience for home, office or laptop users alike.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Laptop users who do not want to bother with having to assemble or carry multiple cables
- Home or office users who would not need to move the eSATA enclosure frequently (fixed distance/location)
- Connect an eSATA enclosure via the more commonly available USB interface

Features

- SuperSpeed USB 3.0 compliant host interface, with supported data transfer rates of up to 5 Gbps
- eSATA interface compliant with SATA revision 2 and other SATA revisions, with supported data transfer rates up to 3 Gbps

- Integrated 1m (3.3ft) USB 3.0 cable and 30cm (1ft) eSATA cable
- No driver or software installation required
- Backward compatible with USB 2.0 systems, with support for USB 2.0 transfer rates of up to 480 Mbps
- Built-in Link/Activity LED indicator
- Plug-and-Play and Hot-Swap compatible

Hardware

Warranty	2 Years
Chipset ID	LucidPort - USB300

Performance

Type and Rate	USB 3.0 - 5 Gbit/s
	SATA II (3 Gbps)
Port Multiplier	No
Max Drive Capacity	Tested up to 2.0 TB

Connector(s)

Drive Connectors	eSATA (7 pin, Data)
Host Connectors	USB Type-A (9 pin) USB 3.0 (5 Gbps)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Special Notes / Requirements

System and Cable Requirements	Available USB port
Note	eSATA port does not support Port Multiplier.

Indicators

LED Indicators	Link/Activity
----------------	---------------

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)



Humidity 5% ~ 85% RH

Physical Characteristics

Color	Black
Material	Plastic
Product Length	4.5 ft [1.4 m]
Weight of Product	2.9 oz [81 g]

Packaging Information

Package Length	6.9 in [17.5 cm]
Package Width	5.5 in [14 cm]
Package Height	1.2 in [30 mm]
Shipping (Package) Weight	4.6 oz [131 g]

What's in the Box

Included in Package	USB 3.0 to eSATA cable
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

