

## SuperSpeed USB 3.0 SATA Adapter Cable for 2.5in or 3.5in Hard Drives

**Product ID:** USB3S2SATA



The USB3S2SATA USB 3.0 to SATA Adapter Cable connects any standard 2.5-inch SATA Hard Drive or Solid State Drive (SSD), or any 3.5-inch SATA hard drive to a computer through USB 3.0.

The USB 3.0 to SATA adapter lets you externally connect a bare drive with no drive enclosure or HDD dock required, saving time, hassle and added cost.

The adapter cable works with Windows, Linux, and Mac computers and does not require any software or driver installation - a true plug-and-play solution for adding cost-effective external storage, or overcoming incompatibility between modern hard drives and motherboards that may not be SATA-equipped or have a Serial ATA port available.

Backed by our 2-year warranty, the USB3S2SATA USB 3.0 to SATA Adapter Cable comes complete with universal adapter and power cords, providing the additional power required to connect 3.5-inch and larger capacity 2.5-inch hard drives.

## Certifications, Reports and Compatibility

### Applications

- Easily connect and access data from a 2.5in or 3.5in hard drive with USB 3.0
- Retrieve data from a hard drive without having to connect the drive internally

### Features

- Maximum transfer rate of 5Gbps using USB 3.0; 480Mbps with USB 2.0
- Compliant with USB specification Rev 2.0 and 3.0

- Compliant with Serial ATA Rev 2.6
- USB attached SCSI protocol (UASP) and Advance Host Controller I/F (AHCI) Rev 1.1 compliant
- Supports both 2.5in and 3.5in SATA Hard Drives (HDDs) and SATA Solid State Drives (SSDs)
- Hot swap and plug and play compatible
- Power button controls

---

#### Hardware

Warranty	2 Years
Number of Drives	1
Compatible Drive Types	SATA
Chipset ID	Symwave - SW6315

---

#### Performance

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

---

#### Connector(s)

Drive Connectors	SATA Data & Power Combo (7+15 pin)
Host Connectors	USB Type-B (9 pin) USB 3.0

---

#### Software

OS Compatibility	Windows XP (32/64-bit)/ Server 2003 (32/64-bit)/ Server 2008 R2/ Vista (32/64-bit)/ 7 (32/64-bit)/ 8 (32/64-bit), Mac OS 10.5.x ~ 10.8 , Linux
------------------	--

---

#### Indicators

LED Indicators	Yellow - Power/Activity
----------------	-------------------------

---

#### Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	5~85% RH

---

#### Physical Characteristics

Color	Black
-------	-------



Material	Plastic
Product Length	2.8 in [70 mm]
Product Width	1.8 in [46 mm]
Product Height	0.8 in [21 mm]
Weight of Product	2.9 oz [82 g]

---

**Packaging Information**

Package Length	8.9 in [22.5 cm]
Package Width	2.2 in [56 mm]
Package Height	6.0 in [15.3 cm]
Shipping (Package) Weight	21.2 oz [600 g]

---

**What's in the Box**

Included in Package	USB 3.0 to SATA Adapter
	1ft USB 3.0 A to B Cable
	EU Power Cord
	UK Power Cord
	Power Adapter and NA Power Cord
	Manual

---

***\*Product appearance and specifications are subject to change without notice.***

