

10 ft Black SuperSpeed USB 3.0 (5Gbps) Cable A to B - M/M

Produkt-ID: USB3SAB10BK



StarTech.com's 10ft Black SuperSpeed USB 3.2 Gen 1 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.2 Gen 1 standard.

Designed for next-generation SuperSpeed USB device connections, the 10ft USB 3.2 Gen 1 cable offers a throughput of up to 5Gbps when used with a USB 3.2 Gen 1 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 10ft USB 3.2 Gen 1 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 10ft USB 3.2 Gen 1 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Connect a SuperSpeed USB 3.0 device to an USB 3.0 capable PC, Notebook, or Server

Merkmale

- Molded connectors with strain relief
- Designed and constructed to SuperSpeed USB 3.2 Gen1 Specifications

Hardware

Garantiebestimmungen	Lifetime
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Typ der Kabelabschirmung	Folie, abgeschirmtes Twisted Pair

Leistung

Typ und Rate	USB 3.0 – 5 Gbit/s
--------------	--------------------

Steckverbinder

Steckverbinder A	1 - USB Type-A (9-polig) USB 3.0 (5 Gbps)
Steckverbinder B	1 - USB 3.2 Typ-B (9-polig, Gen 1, 5Gbit/s)

Umgebungsbedingungen

Betriebstemperatur	-10°C to 50°C (14°F to 122°F)
Lagertemperatur	-20°C to 60°C (-4°F to 140°F)
Feuchtigkeit	0~75% RH

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	28 AWG
Kabellänge	10.0 ft [3.0 m]
Produktlänge	10.0 ft [3.0 m]
Produktbreite	0.5 in [1.4 cm]
Produkthöhe	0.5 in [1.2 cm]
Produktgewicht	4.6 oz [129.7 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	7.1 in [18.1 cm]
Paketbreite	5.9 in [15.0 cm]
Pakethöhe	1.1 in [2.8 cm]
Versandgewicht (Verpackung)	4.9 oz [138.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 10ft black USB 3.0 A to B cable
--------------------	-------------------------------------

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.