

90 cm SuperSpeed USB3.0 Kabel - USB-A naar USB-B - M/M - Zwart

Productcode: USB3SAB3BK



StarTech.com's 3ft Black SuperSpeed USB 3.0 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, the 3ft USB 3.0 cable offers a throughput of up to 5Gbps when used with a USB 3.0 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 3ft USB 3.0 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 3ft USB 3.0 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certificaties, rapporten en compatibiliteit

Toepassingen

- Connect a SuperSpeed USB 3.0 device to an USB 3.0 capable PC, Notebook, or Server

Eigenschappen

- Designed and constructed to SuperSpeed USB 3.0 Specifications
 - Molded connectors with strain relief
-

Hardware

Garantiebeleid	Lifetime
Type kabelmantel	PVC - Polyvinyl Chloride
Kabelafscherming	Folie afgeschermd getwist paar

Prestaties

Type en snelheid	USB 3.0 - 5 Gbit/s
------------------	--------------------

Connector(en)

Connector A	USB Type-A (9-polig) USB 3.0 (5 Gbps)
Connector B	USB Type-B (9-polig) USB 3.0

Gebruiksomgeving

Bedrijfstemperatuur	-10°C to 50°C (14°F to 122°F)
Opslagtemperatuur	-20°C to 60°C (-4°F to 140°F)
Vochtigheid	0~75% RH

Fysieke eigenschappen

Kleur	Zwart
Draaddikte	28 AWG
Kabellengte	36.0 in [91.4 cm]
Lengte product	36.0 in [91.4 cm]
Breedte product	0.0 in [0.0 mm]
Hoogte product	0.0 in [0.0 mm]
Gewicht product	1.9 oz [53.0 g]

Verpakkingsinformatie

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.8 in [21.0 mm]



Verzendgewicht (verpakt)	2.0 oz [58.0 g]
-----------------------------	-----------------

Wat wordt er
meegeleverd

Meegeleverd	3ft black USB 3.0 A to B cable
-------------	--------------------------------

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.

