

3m Black SuperSpeed USB 3.0 Cable - Right Angle A to B - M/M

Produkt ID: USB3SAB3MRA



The USB3SAB3MRA 3m Black USB 3.0 A to B cable features a right-angled USB 'A' male connector, enabling you to connect your USB 3.0 Type 'B' peripherals to your PC, laptop, or server, even in hard to reach areas and tight spaces.

The right-angled USB 'A' connector positions the cable nearly flush against a wall or other surface, and eliminates the space typically required to accommodate a 'straight' connection from the cable into the USB port.

Harnessing the full capabilities of the SuperSpeed USB 3.0 standard when used with a USB 3.0 host and device, the 3m cable offers a bandwidth of 5Gbps.

Plus, this right angle USB 3.0 cable also features high quality Shielded Twisted Pair (STP) construction, which helps prevent electro-magnetic interference and ensure reliable data communication.

The USB3SAB3MRA USB 3.0 A to B cable is backed by StarTech.com's Lifetime Warranty, for guaranteed quality and dependability.

Certifikat, rapporter och kompatibilitet

Användning

- Connect a SuperSpeed USB 3.0 Type B peripheral (hard drive enclosure, card reader, docking station, video capture device, etc.) to a USB 3.0 capable desktop, laptop, or server, even in hard to reach areas and tight spaces

Funktioner

- 1x Right-angled USB 3.0 'A' male connector
- 1x USB 3.0 'B' male connector
- Designed and constructed to SuperSpeed USB 3.0 Specifications
- High quality Shielded Twisted Pair (STP) construction
- Data transfer rates up to 5Gbps
- Molded connectors with strain relief
- Backward compatible with USB 2.0

Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Folieskärmad partvinnad

Prestanda

Typ och hastighet	USB 3.0 - 5 Gbit/s
-------------------	--------------------

Kontakt(er)

Connector A	USB Type-A (9-stifts) USB 3.0 (5 Gbps)
Connector B	USB Type-B (9-stifts) USB 3.0

Utseende

Färg	Svart
Kontakttyp	Rak till högervinklad
Tråddimension	28 AWG
Kabellängd	9.8 ft [3 m]
Produktlängd	9.8 ft [3 m]
Produktbredd	0.4 in [11 mm]



Produkt höjd	0.6 in [14 mm]
Produkt vikt	4.1 oz [116 g]

Förpackning

Förpackningsantal	1
Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.5 in [12 mm]
Fraktvikt (förpackning)	4.4 oz [124 g]

Vad det är i lådan

Ingår i paketet	3m Black SuperSpeed USB 3.0 Cable Right Angle A to B - M/M
-----------------	--

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

