

3 ft SuperSpeed USB 3.0 (5Gbps) Cable A to Micro B

Produkt-ID: USB3SAUB3



The USB3SAUB3 3-foot SuperSpeed USB 3.2 Gen 1 Cable (A to Micro B) offers a durable, high quality connection that harnesses the full capability of the USB 3.2 Gen 1 standard.

Designed for next-generation SuperSpeed USB device connections, the USB 3.2 Gen 1 A to Micro B cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication to provide a quick and easy way to connect to an external storage solution with astounding throughputs of up to 5Gbps (when used with a USB 3.2 Gen 1 host and device).

The 3-foot USB 3.2 Gen 1 A to Micro B cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Connecting Micro USB 3.0 devices to a SuperSpeed USB 3.0 compatible PC or Laptop

Merkmale

- Shielded Twisted Pair (STP) design, helping to eliminate electro-magnetic interference (EMI)

- Data transfer rates up to 5Gbps
- Backwards compatible with USB 2.0
- Molded connectors with strain relief

Hardware

Garantiebestimmungen	Lifetime
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht

Leistung

Typ und Rate	USB 3.0 – 5 Gbit/s
--------------	--------------------

Steckverbinder

Steckverbinder A	1 - USB Type-A (9-polig) USB 3.0 (5 Gbps)
Steckverbinder B	1 - USB 3.0 Micro-B (10-polig, SuperSpeed)

Physische Eigenschaften

Farbe	Blau
Drahtstärke	28 AWG
Kabellänge	3.0 ft [0.9 m]
Produktlänge	36.0 in [91.4 cm]
Produktbreite	0.0 in [0.0 mm]
Produkthöhe	0.0 in [0.0 mm]
Produktgewicht	1.5 oz [43.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	6.9 in [17.6 cm]

Paketbreite 7.8 in [19.9 cm]

Pakethöhe 0.7 in [1.7 cm]

Versandgewicht
(Verpackung) 1.8 oz [52.0 g]

Verpackungsinhalt

Im Paket enthalten 1 - 3 ft SuperSpeed USB 3.0 Cable A to Micro B

Garantieinformationen

Warranty Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.