

Micro-USB Cable - M/M - 1m, Green

Product ID: USBAUB1MGN



Tired of the same old boring black cables? Want something that matches your personality?

The USBAUB1MGN 1m Green Micro USB Cable is perfect for adding a little color to your life, and for providing a reliable solution for charging and syncing your Micro USB mobile devices. Plus, the cable offers a slim design that lets you plug into your device without having to take it out of its case for every charge and sync.

The cable is colored to suit your green mobile devices but it can be used with any of your Micro USB-enabled mobile devices – so don't be afraid to be colorful and select from any of our colored Micro USB cables such as Pink, Green, Yellow or Blue. You can create the perfect color match with your smartphone or tablet or be creative with your own unique look!

Replace the cable that came with your device and keep one as a spare in your laptop bag, backpack or other carrying case.

Stop removing the case from your phone or tablet every time you charge or sync your device. The cable offers a slim Micro USB connector molding that plugs into your device even while it's inside a protective case.

Designed and constructed for maximum durability, this high quality USB-A to Micro-B cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Charge and sync your Micro USB-equipped mobile digital devices
- Replace the cable that came with your device or keep one as a spare while traveling

Features

- Stylish green design
- Slim Micro USB connector molding
- Aluminum-mylar foil with braided shielding
- Supports high-speed USB data transfer rates of up to 480 Mbps

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	USB Type-A (4 pin) USB 2.0
Connector B	USB Micro-B (5 pin)

Special Notes / Requirements

Note	Micro USB connector molding width is 10mm and height is 6mm (please see drawing)
------	--

Physical Characteristics

Color	Green
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	39.4 in [100 cm]
Product Length	39.4 in [100.0 cm]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]

Weight of Product	0.8 oz [22.0 g]
-------------------	-----------------

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.6 in [14.0 mm]
Shipping (Package) Weight	1.0 oz [27.0 g]

What's in the Box

Included in Package	1m Green Mobile Charge Sync Micro USB Cable - A to Micro B
---------------------	--

****Product appearance and specifications are subject to change without notice.***

