


Micro-USB Cable - M/M - 2m

Product ID: USBAUB2MBK



Tired of being attached to the wall when charging and using your phone or tablet?

The USBAUB2MBK Micro USB cable offers 2 meters in cable length so you can charge your device in comfort and from a distance. Plus, the cable offers a slim design that lets you plug into your device without having to take it out of its case for every charge and sync.

Charge your device even while you're taking notes in a boardroom, catching up on emails in a hotel room, or reading in a coffee shop. The 2-meter long charge cable overcomes distance restrictions and lets you stay connected even while charging.

Stop removing the case from your phone or tablet every time you charge or sync your device. The cable offers a slim Micro USB connector molding that plugs into your device even while it's inside a protective case.

Designed and constructed for maximum durability, this high quality USB-A to Micro-B cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Charge and sync your Micro USB-equipped mobile digital devices

Features

- Slim Micro USB connector molding
- Aluminum-mylar foil with braided shielding
- Supports high-speed USB data transfer rates of up to 480 Mbps

Hardware

| | |
|-----------------------|--------------------------------|
| Warranty | Lifetime |
| Connector Plating | Nickel |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

Performance

| | |
|---------------|----------------------|
| Type and Rate | USB 2.0 - 480 Mbit/s |
|---------------|----------------------|

Connector(s)

| | |
|-------------|-------------------------------------|
| Connector A | 1 - USB 2.0 Type-A (4 pin, 480Mbps) |
| Connector B | 1 - USB Micro-B (5 pin) |

Special Notes / Requirements

| | |
|------|--|
| Note | Micro USB connector molding width is 10mm and height is 6mm (please see drawing) |
|------|--|

Physical Characteristics

| | |
|-------------------|-----------------|
| Color | Black |
| Connector Style | Straight |
| Wire Gauge | 28 AWG |
| Cable Length | 6.6 ft [2 m] |
| Product Length | 6.6 ft [2.0 m] |
| Product Width | 0.2 in [0.5 cm] |
| Product Height | 0.2 in [0.5 cm] |
| Weight of Product | 1.7 oz [47.0 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Quantity | 1 |
| Package Length | 8.9 in [22.5 cm] |
| Package Width | 4.7 in [12.0 cm] |
| Package Height | 0.4 in [10.0 mm] |
| Shipping (Package) Weight | 1.7 oz [48.0 g] |

What's in the Box

| | |
|---------------------|--|
| Included in Package | 1 - 2m Mobile Charge Sync Micro USB Cable - A to Micro B |
|---------------------|--|

****Product appearance and specifications are subject to change without notice.***