

3ft (1m) USB-C Cable with USB-A Adapter Dongle - Hybrid 2-in-1 USB C Cable w/ USB-A - USB-C to USB-C (10Gbps/100W PD), USB-A to USB-C (5Gbps) - Ideal for Hybrid Docking Station

**Product ID:** USBCCADP



This hybrid 1-meter USB-C to C, USB 3.2 Gen 2 (10Gbps) cable with attached USB-A to C, USB 3.2 Gen 1 (5Gbps) adapter lets you connect a USB Type-C device, such as a docking station, hard drive, tablet or mobile device, to the USB-C or USB-A port on your host computer. The cable is also compatible with Thunderbolt 3 ports.

Note: When used with a USB-A host this cable will only work with docks that support DisplayLink.

Charge your USB Type-C devices faster

When used with a PD 3.0 enabled USB-C power source, the 1-meter USB-C to C cable supports up to 100W (5Amps) of power to charge a USB-C or Thunderbolt 3 laptop, tablet or smart phone.

Attached USB-C to USB-A adapter when paired with the USB-C to C cable also supports up to 15W (5V, 3Amps) of power to charge your devices from a USB-A wall charger, car charger or power bank -- perfect for people on the move, for providing simple, tidy connections.

Connect your USB 3.1 peripherals

The USB 3.2 Gen 2, USB-C to C cable offers 10Gbps data rate, enabling you to sync your USB Type-C devices in no time at all. You'll also be able to connect your USB 3 (3.0, 3.1 or 3.2) peripheral devices, such as hard drive enclosures and docks, to your USB-C or TB3 laptop.

USB 3.2 Gen 1, USB-C to A adapter, when used with the USB-C to C cable, offers 5Gbps data rate. You can spend less time transferring and backing up your data from your USB-C devices to your USB-A host and focus more on your projects and presentations.

Hybrid Docking Station cable

Use this cable with your Hybrid USB-C Docking Station or USB-C Hub to connect your laptop, tablet, smart phone or portable drives. This cable also comes as an accessory for StarTech.com's Hybrid Dual Monitor (4K 60Hz) Docking Stations such as DK30C2DPEP, DK30C2DPPD, and DK31C3HDPD.

The USBCCADP is backed by StarTech.com's 2-year warranty for guaranteed reliability.

## Certifications, Reports and Compatibility

### Applications

### Features

- **HYBRID 2-IN-1 USB C CABLE WITH USB A ADAPTER:** This USB-C to C cable with a built-in USB-C to A Adapter; connects your USB-C, Thunderbolt 3 or USB-A host with a USB-C device; Allows you to connect, transfer data, and charge your USB-C or TB3 laptop
- **HIGH PERFORMANCE CABLE:** The 3.3ft (1m) USB-C to C cable complies w/ USB 3.2/3.1 Gen 2 SuperSpeed+ (10Gbps); attached USB-C to A adapter dongle complies w/ USB 3.2/3.1 Gen 1 (5Gbps); Ideal for connecting your USB-A or C host to your USB Type-C dock
- **USB-C POWER DELIVERY:** USB-C to USB-C cable for docking stations that supports up to 100W PD 3.0 to charge a TB3 or USB-C workstation laptop: MacBook Air/Pro, Dell Latitude/Precision/XPS, Surface Book/Pro, Lenovo ThinkPad X1 Carbon, HP Spectre/Envy/ZBook
- **COMPATIBLE WITH HYBRID USB C DOCKS:** Combo USB-C with USB-A cable ideal for a universal USB-C hybrid dock or USB-C hub; USB-C host works w/ any USB-C dock, USB-A host works w/ DisplayLink docks only; Replacement/accessory cable for DK30C2DPEP/DK30C2DPPD
- **CABLE SPECS:** Length: 3.3ft (1m) Black USB-C to USB-C M/M cable w/ USB-C to A adapter (Female/Male) Performance: USB 3.1 Gen 2 (cable), USB 3.0 (adapter) Power: 100W (cable) Jacket: PVC EMI Shield: Al-Mylar Backed for 2-Years by StarTech.com

---

#### Hardware

Warranty	2 Years
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

#### Performance

Type and Rate	USB 3.2 Gen 2 - 10 Gbit/s
	USB 3.1 Gen 1 - 5 Gbit/s

---

#### Connector(s)

Connector A	USB Type-C (24 pin) USB 3.1 (10Gbps)
	USB Type-C (24 pin) USB 3.0 (5Gbps)
Connector B	USB Type-C (24 pin) USB 3.1 (10Gbps)

USB Type-A (9 pin) USB 3.0 (5 Gbps)

---

**Power**

Power Delivery	100W
----------------	------

---

**Environmental**

Operating Temperature	0C to 125C (32F to 257F)
-----------------------	--------------------------

Storage Temperature	-55C to 125C (-67F to 257F)
---------------------	-----------------------------

---

**Physical Characteristics**

Cable Length	39.4 in [100 cm]
--------------	------------------

Product Length	39.4 in [100.0 cm]
----------------	--------------------

Product Width	0.8 in [20.0 mm]
---------------	------------------

Product Height	0.3 in [7.0 mm]
----------------	-----------------

Weight of Product	1.9 oz [54.0 g]
-------------------	-----------------

---

**Packaging Information**

Package Length	8.4 in [21.3 cm]
----------------	------------------

Package Width	0.8 in [20.0 mm]
---------------	------------------

Package Height	0.3 in [7.0 mm]
----------------	-----------------

Shipping (Package) Weight	2.3 oz [64.0 g]
---------------------------	-----------------

---

**What's in the Box**

Included in Package	USB-C Cable
---------------------	-------------

---

*\*Product appearance and specifications are subject to change without notice.*

