

2m White USB 2.0 Extension Cable A to A - M/F

Produkt ID: USBEXTPAA2MW



The USBEXTPAA2MW 2m White USB 2.0 Extension Cable features a USB 'A' male connector and a USB 'A' female connector, enabling you to extend the connection distance between your USB 2.0 devices by up to 1-meter – allowing for better placement of your peripheral devices, or adding flexibility to your existing USB ports.

The cable features thin USB connector moldings which allow you to simplify your connections, and plug into tight fitting locations.

Designed and constructed for maximum durability, this high quality USB 2.0 extension cable is backed by StarTech.com's Lifetime Warranty.

Certifikat, rapporter och kompatibilitet



Användning

- Extend the length of your USB 2.0 A to B cable by up to 2m – for convenient placing of your USB 2.0 peripherals

Funktioner

- 1x USB 'A' male connector

- 1x USB 'A' female connector
- Thin USB 2.0 connector moldings, with strain relief
- All white construction
- Supports high-speed data transfer rates of up to 480 Mbps

Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med jord-tråd

Prestanda

Typ och hastighet	USB 2.0 - 480 Mbit/s
-------------------	----------------------

Kontakt(er)

Connector A	1 - USB 2.0 Type-A (4 stift, 480 Mbps)
Connector B	1 - USB 2.0 Type-A (4 stift, 480 Mbps)

Miljö

Drifttemperatur	-20°C to 60°C (-4°F to 140°F)
Förvaringstemperatur	-10°C to 30°C (14°F to 86°F)
Luftfuktighet	30%-75% RH

Utseende

Färg	Vit
Kontakttyp	Rak
Tråddimension	24/28 AWG
Kabellängd	6.6 ft [2 m]
Produktlängd	6.6 ft [2.0 m]
Produktbredd	0.7 in [1.7 cm]

	Produkthöjd	0.4 in [0.9 cm]
	Produktvikt	1.4 oz [40.0 g]
Förpackning	Förpackningsantal	1
	Paketets längd	8.9 in [22.5 cm]
	Paketets bredd	4.9 in [12.5 cm]
	Paketets höjd	0.0 in [0.1 mm]
	Fraktvikt (förpackning)	1.6 oz [46.0 g]
Vad det är i lådan	Ingår i paketet	1 - 2m White USB Extension Cable - A to A M/F
Warranty Information	Warranty	Livslängd

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.