

15 ft 4-in-1 USB DVI KVM Switch Cable w/ Audio & Microphone

Produkt ID: USBDVI4N1A15

The USBDVI4N1A15 15 ft 4-in-1 USB DVI KVM Cable with Audio and Microphone integrates DVI video quality with USB mouse, keyboard, 3.5mm audio out and microphone connections into a single, compact cable.

The 4-in-1 KVM cable is a cost-effective and convenient solution that's suitable for use with DVI supported USB KVM switches, allowing you to share a USB peripheral set between two computers configured for high definition output.

Backed by a StarTech.com Lifetime Warranty.

Works with:

Compatible StarTech.com KVMs can be found under the Accessories section.

Aten models (CS1642, CS1644, CS1784, CS1782, CS1762, CS1764)

Avocent models (2SVDVI10-001, 4SVDVI10-001, SV4UAD, SC420, SC440, SC540)

Belkin models (F1DN102D, F1DN104D, F1DD102L, F1DD104L)

Cables to go models (52047, 52048)

Certifikat, rapporter och kompatibilitet



Användning

- Connects a computer to a DVI + USB KVM switch with audio and mic support

Funktioner

- Combines 4 peripheral cables into one
- Supports a maximum resolution of 1920x1200
- Meets and exceeds all DVI-I and USB 2.0 specifications

Kontakt(er)

Garantipolicy	Lifetime
Connector A	2 - 3.5 mm minijack (3-polig) 1 - DVI-I (29-stifts) 1 - USB 2.0 Type-A (4 stift, 480 Mbps)
Connector B	2 - 3.5 mm minijack (3-polig) 1 - DVI-I (29-stifts) 1 - USB B (4-stifts)

Utseende

Färg	Svart
Kabellängd	15.0 ft [4.6 m]
Produktlängd	15.0 ft [4.6 m]
Produktbredd	0.0 in [0.0 cm]
Produkthöjd	0.0 in [0.0 cm]
Produktvikt	2.6 lb [1.2 kg]

Förpackning

Förpackningsantal	1
Paketets längd	10.1 in [25.6 cm]
Paketets bredd	1.4 in [3.6 cm]
Paketets höjd	12.2 in [31.0 cm]
Fraktvikt (förpackning)	2.6 lb [1.2 kg]

Vad det är i lådan

Ingår i paketet	1 - USB, DVI and Audio KVM Cable
-----------------	----------------------------------

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.