

2m White Micro USB Cable - A to Micro B

Produkt ID: USBPAUB2MW



The USBPAUB2MW 2m White USB to Micro USB Cable features thin USB connector moldings and provides a simpler connection between your Micro USB 2.0 mobile devices (smartphones, digital cameras, Tablet PC devices, portable hard drives, etc.) and your PC or Mac® computer, for everyday tasks such as charging, data synchronization or file transfers.

Designed and constructed for maximum durability, this high quality USB-A to Micro-B replacement cable is backed by StarTech.com's Lifetime Warranty.

Certifikat, rapporter och kompatibilitet



Användning

- Transfer data and provide power while charging your Micro USB device
- An ideal replacement cable for connecting Micro USB mobile devices to a USB-capable computer

Funktioner

- 1x USB 'A' male connector
- 1x USB Micro-B male connector

- Thin USB 2.0 connector moldings, with strain relief
- All white construction
- Supports high-speed data transfer rates of up to 480 Mbps
- Offers 2m in cable length

Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med jord-tråd

Prestanda

Typ och hastighet	USB 2.0 - 480 Mbit/s
-------------------	----------------------

Kontakt(er)

Connector A	1 - USB 2.0 Type-A (4 stift, 480 Mbps)
Connector B	1 - USB Micro-B (5-stifts)

Miljö

Drifttemperatur	-20°C to 60°C (-4°F to 140°F)
Förvaringstemperatur	-10°C to 30°C (14°F to 86°F)
Luftfuktighet	30%-75% RH

Utseende

Färg	Vit
Kontakttyp	Rak
Tråddimension	28 AWG
Kabellängd	6.6 ft [2 m]
Produktlängd	6.6 ft [2.0 m]
Produktbredd	0.5 in [1.2 cm]

	Produkthöjd	0.2 in [0.5 cm]
	Produktvikt	1.0 oz [28.0 g]
Förpackning	Förpackningsantal	1
	Paketets längd	6.5 in [16.5 cm]
	Paketets bredd	5.0 in [12.6 cm]
	Paketets höjd	0.5 in [1.3 cm]
	Fraktvikt (förpackning)	1.2 oz [34.0 g]
Vad det är i lådan	Ingår i paketet	1 - 2m White Micro USB Cable - A to Micro B
Warranty Information	Warranty	Livslängd

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.