

6ft Micro USB Cable - A to Micro B

Productcode: UUSBHAUB6



The UUSBHAUB6 6-foot USB A to Micro USB cable features one USB 'A' male connector, and one 'Micro-B' male connector, providing a high quality connection to USB 2.0 mobile devices (such as BlackBerry® or Android-based cellular phones, digital cameras, Tablet PC devices and GPS systems) that use a Micro USB connector to a USB capable computer for everyday tasks such as data synchronization and file transfers.

This high quality cable is backed by StarTech.com's Lifetime Warranty to ensure dependable, long-lasting connections between Micro USB and USB devices.

Certificaties, rapporten en compatibiliteit



Toepassingen

- An ideal replacement cable for connecting mobile devices to a USB capable computer

Eigenschappen

- Supports high speed data transfer rates up to 480 Mbps
- Aluminum-Mylar Foil with Braided Shielding

- High quality USB 'A' and USB 'Micro-B'connectors
- Durable PVC construction

Hardware

Garantiebeleid	Lifetime
Connectormateriaal	Nikkel
Type kabelmantel	PVC - Polyvinyl Chloride
Kabelafscherming	Aluminium-Mylar folie met vlechtwerk

Prestaties

Type en snelheid	USB 2.0 - 480 Mbit/s
------------------	----------------------

Connector(en)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB Micro-B (5-polig)

Gebruiksomgeving

Bedrijfstemperatuur	-20°C to 60°C (-4°F to 140°F)
Opslagtemperatuur	-10°C to 30°C (14°F to 86°F)
Vochtigheid	30%-75% RH

Fysieke eigenschappen

Kleur	Zwart
Draaddikte	28 AWG
Kabellengte	6.0 ft [1.8 m]
Lengte product	6.0 ft [1.8 m]
Breedte product	0.6 in [1.6 cm]
Hoogte product	0.3 in [0.7 cm]
Gewicht product	1.6 oz [46.0 g]

Verpakkingsinform

atie

Verpakkingsaantal	1
Lengte Verpakking	5.3 in [13.5 cm]
Package Width	5.0 in [12.6 cm]
Package Height	0.6 in [1.6 cm]
Verzendgewicht (verpakt)	1.7 oz [48.0 g]

Wat wordt er
meegeleverd

Meegeleverd	1 - 6ft Micro USB Cable - A to Micro B
-------------	--

Garantiebepalinge
n

Warranty	Levenslang
----------	------------

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.