

VGA to HDMI Scaler - 1920x1200 - TAA

**Product ID:** VGA2HDPRO2



This VGA to HDMI converter and scaler lets you connect your analog VGA video signal to a digital HDMI display. It features a built-in video scaler that adjusts the output signal to suit virtually any HDMI display. It scales the signal to your choice of resolutions, up to 1080p.

The converter and scaler features 3.5mm and optical audio inputs, which let you combine audio into the HDMI output. The scaler creates a digital signal at high resolutions that's perfect for updating legacy VGA video equipment to work with newer HDMI televisions or projectors.

New HDMI displays are phasing out support for lower resolution video signals such as 480i, 480p, and 720p. Without support for these common VGA resolutions, you may not be able to use a standard adapter to connect your legacy video output to your new display.

This converter lets you continue using your current VGA source equipment by scaling your video signal to a resolution that's compatible with your new HDMI display. Scaling your source enables you to upgrade to a sleek new HDMI display while keeping your tried-and-true source material on display at trade shows and storefronts.

Upgrading every component in your A/V setup can be costly and time consuming. Retaining your source can save you the cost and hassle of buying and configuring new equipment. With the VGA to HDMI converter, you can bridge the gap between old and new technologies by converting your dependable VGA source to high-resolution HDMI.

This converter features automatic resolution detection that minimizes your setup time by avoiding tedious programming. Plus, it features an intuitive on-screen menu that lets you customize the parameters of your input to quickly select and compare different output options, ensuring you get the best video solution possible in a very short time period.

Notes: This converter does not output digitally-encrypted content. This converter is the direct replacement for VGA2HDMIPRO.

The VGA2HDPRO2 and is backed by a 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Convert analog video and audio to digital HDMI content
- Add your VGA video source to a video distribution solution, that only accepts digital content
- Watch content from an older computer on an HD TV

## Features

- Customize your analog VGA source to work with any HDMI display, with the built-in video scaler
- Avoid upgrading your VGA equipment by scaling your source to an HDMI display
- Enjoy hassle-free operation with an intuitive on-screen menu and automatic display detection
- Supports high-definition resolutions up to 1920x1200 or 1080p
- Supports 3.5mm analog audio or SPDIF digital audio inputs

---

### Hardware

Warranty	2 Years
Active or Passive Adapter	Active
AV Input	VGA
	3.5 mm Stereo Audio
	Toslink
AV Output	HDMI
	3.5 mm Stereo Audio
	Toslink

Audio Yes

---

**Performance**

Maximum Analog Resolutions	1920 x 1200
Supported Resolutions	Widescreen(16/32 bit):  1920x1200, 1920x1080, 1680x1050, 1366x768, 1280x800, 1280x768, 1280x720  Standard(16/32 bit):  1600x1200, 1400x1050, 1280x1024, 1024x768, 800x600, 640x480
Wide Screen Supported	Yes
Audio Specifications	2-Channel Stereo audio (3.5mm)  7.1-channel surround sound audio (SPDIF)

---

**Connector(s)**

Connector A	1 - VGA (15 pin, High Density D-Sub)  1 - 3.5mm Mini-Jack (3 Position) / Mini-Toslink (SPDIF, Optical)  1 - Toslink (SPDIF, Optical)
Connector B	1 - HDMI (19 pin)  1 - 3.5 mm Mini-Jack (3 Position)  1 - Toslink (SPDIF, Optical)

---

**Indicators**

LED Indicators	1 - Power LED
----------------	---------------

---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.6 A
Output Voltage	5 DC
Output Current	2.6 A

Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	13

---

#### Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	20~90% RH (non-condensing)

---

#### Physical Characteristics

Color	Black
Material	Steel
Product Length	5.8 in [14.7 cm]
Product Width	4.0 in [10.2 cm]
Product Height	1.0 in [2.5 cm]
Weight of Product	11.5 oz [326.0 g]

---

#### Packaging Information

Package Quantity	1
Package Length	11.2 in [28.4 cm]
Package Width	7.2 in [18.4 cm]
Package Height	2.8 in [7.0 cm]
Shipping (Package) Weight	2.0 lb [0.9 kg]

---

#### What's in the Box

Included in Package	1 - VGA to HDMI Converter / Scaler
	1 - 4ft (1.2m) VGA Cable
	1 - 6ft (1.8m) 3.5mm to RCA Cable
	1 - Universal Power Adapter (NA/EU/UK/AU)

1 - Quick install guide

---

***\*Product appearance and specifications are subject to change without notice.***

