

VGA to HDMI Adapter with USB Audio & Power – Portable VGA to HDMI Converter – 1080p

Product ID: VGA2HDU



The VGA2HDU VGA to HDMI adapter lets you turn the VGA port on your Desktop or Laptop computer into an HDMI output port.

With the VGA2HDU, you can expand your VGA video output to accommodate the increasing number of displays and projectors that only support HDMI.

Not all VGA converters are created equal. This adapter ensures you're harnessing the highest video quality from your VGA output, with support for resolutions up to 1920x1080 (1080p).

For hassle-free setup the VGA to HDMI adapter allows for plug-and-play installation. Plus, with a built-in USB power cable the device is powered using the USB port on your computer. The VGA to HDMI adapter will work with any computer operating system, but when working with a Windows computer the adapter supports native USB audio, allowing you to add your computer audio to the HDMI signal.

The VGA2HDU is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connect your VGA-equipped computer to an HDMI home theatre system
- Share video content from your VGA-equipped computer on an HDMI television or projector
- Connect a legacy VGA-equipped device to a newer HDMI display
- Share audio from your Windows based PC

Features

- USB audio
- Supports video resolutions up to 1920x1080
- Compact, lightweight design
- Plug-and-play installation
- USB powered

Hardware

Warranty	2 Years
Active or Passive Adapter	Active
AV Input	VGA
AV Output	HDMI
Cabling	HDMI
Audio	Yes
Chipset ID	Micro Silicon - MS9282

Performance

Maximum Analog Resolutions	1920x1080
Maximum Digital Resolutions	1920x1080
Supported Resolutions	1920x1080 (1080p)
	1680x1050 (WSXGA+)
	1600x1200
	1600x900
	1440x900
	1400x1050 (SXGA+)
	1366x768
	1360x768
	1280x1024



1280x960
1280x800
1280x768 (WXGA)
1280x720p (720p)
1280x600
1152x864
1024x768
800x600 (SVGA)
640x480 (480p)

Wide Screen Supported Yes
MTBF 1,063,669 hours

Connector(s)

Connector A VGA (15 pin, High Density D-Sub)
USB Type-A (4 pin) USB 2.0
Connector B HDMI (19 pin)

Special Notes / Requirements

Note When used with a Windows computer this adapter supports native USB audio.

If used with a computer, volume levels cannot be adjusted using the operating system. Volume levels can be controlled by the output device (TV, speakers, audio receiver, etc).

Power

Power Source USB-Powered

Environmental

Operating Temperature 0C to 60C (32F to 140F)
Storage Temperature -10C to 70C (14F to 158F)
Humidity 40%-85%RH

Physical Characteristics

Color Black



Material	Plastic
Product Length	10.2 in [26 cm]
Product Width	1.4 in [35 mm]
Product Height	0.6 in [15 mm]
Weight of Product	2.5 oz [70.7 g]

Packaging Information

Package Length	6.8 in [17.3 cm]
Package Width	5.7 in [14.4 cm]
Package Height	1.2 in [30 mm]
Shipping (Package) Weight	5.3 oz [151 g]

What's in the Box

Included in Package	VGA to HDMI adapter w/ USB power & audio
	2ft USB Extension Cable

****Product appearance and specifications are subject to change without notice.***

