

3 Port HDMI Auto Switch w/ IR Remote Control

Produkt ID: VS123HD



The VS123HD 3-port HDMI® Auto Switch features three prioritized HDMI input ports. If the active HDMI source is turned off, disconnected, or otherwise lost, the switch automatically selects the next available HDMI signal as the priority output, ensuring the display is always receiving a signal.

The automatic switch includes an IR Remote Control, so you'll be able to share an HD projector or display between three HDMI audio/video sources, with the option to manually control the switch from a distance or through the easy-to-use front panel toggle button.

Ideal for High-Definition applications, this 3-in/1-out HDMI switch supports true High-Definition 1080p resolutions (WUXGA/1920x1200 from PC/computer) as well as 7.1 Surround Sound audio, ensuring the best possible multimedia experience from connected devices.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet



Användning

- Switching between High-Definition audio-video devices e.g Blu-ray players, satellite receivers, video game consoles or computers with HDMI output
- Digital signage scenarios that require a signal always be available to a display

Funktioner

- Transparent, automatic HDMI switching
- IR remote control
- Built-in HDMI display cable saves you from purchasing an additional cable
- Supports HDTV resolutions up to 1080p
- Supports PC resolutions up to 1920x1200
- Easy installation and set up in minutes
- Allows for cables up to 30ft (10m) in length
- Supports High Speed HDMI device switching
- HDCP Compliant
- Supports 3D Video

Hårdvara

Garantipolicy	2 Years
AV-ingång	HDMI
Portar	3
AV-utgång	HDMI
Audio	Ja
Industristandarder	High Speed HDMI®, HDCP

Prestanda

Maximalt avstånd	10m [33ft]
Maximal digital upplösning	1920x1200
Stöd för widescreen	Ja

Kontakt(er)

Connector A	1 - HDMI (19-stifts)
-------------	----------------------

Connector B		3 - HDMI (19-stifts)
Särskilda anmärkningar/krav		
	Obs.	Port 1 is set to have higher priority than port 2 or port 3 when all signals are on. Port 2 is set to have higher priority than port 3 when both signals are on, but Port 1 is off.
Indikatorer		
	LED-indikatorer	3 - Two Green for Display Status, and one red for power.
Miljö		
	Drifttemperatur	0°C to 70°C (32°F to 158°F)
	Förvaringstemperatur	-65°C to 150°C (-85°F to 302°F)
	Luftfuktighet	10% to 85%RH
Utseende		
	Färg	Svart
	Kabinettyp	Av plast
	Produktlängd	3.2 in [81 mm]
	Produktbredd	2.2 in [5.5 cm]
	Produkthöjd	1.0 in [2.5 cm]
	Produktvikt	2.4 oz [68 g]
Förpackning		
	Förpackningsantal	1
	Paketets längd	8.3 in [21 cm]
	Paketets bredd	5.7 in [14.5 cm]
	Paketets höjd	1.6 in [40 mm]
	Fraktvikt (förpackning)	7.6 oz [214 g]
Vad det är i lådan		

Ingår i paketet	1 - 3 Port High Speed HDMI® Auto Switch
	1 - Remote Control
	1 - IR Extender Cable
	1 - Instruction Manual

Warranty
Information

Warranty	2 År
----------	------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.