

## 3 Port HDMI Auto Switch w/ IR Remote Control

**Product ID:** VS123HD



The VS123HD 3-port HDMI Auto Switch features three prioritized HDMI input ports. If the active HDMI source is turned off, disconnected, or otherwise lost, the switch automatically selects the next available HDMI signal as the priority output, ensuring the display is always receiving a signal.

The automatic switch includes an IR Remote Control, so you'll be able to share an HD projector or display between three HDMI audio/video sources, with the option to manually control the switch from a distance or through the easy-to-use front panel toggle button.

Ideal for High-Definition applications, this 3-in/1-out HDMI switch supports true High-Definition 1080p resolutions (WUXGA/1920x1200 from PC/computer) as well as 7.1 Surround Sound audio, ensuring the best possible multimedia experience from connected devices.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Switching between High-Definition audio-video devices e.g Blu-ray players, satellite receivers, video game consoles or computers with HDMI output
- Digital signage scenarios that require a signal always be available to a display

### Features

- Transparent, automatic HDMI switching

- IR remote control
- Built-in HDMI display cable saves you from purchasing an additional cable
- Supports HDTV resolutions up to 1080p
- Supports PC resolutions up to 1920x1200
- Easy installation and set up in minutes
- Allows for cables up to 30ft (10m) in length
- Supports High Speed HDMI device switching
- HDCP Compliant
- Supports 3D Video

---

#### Hardware

Warranty	2 Years
AV Input	HDMI
Ports	3
AV Output	HDMI
Audio	Yes
Industry Standards	High Speed HDMI, HDCP

---

#### Performance

Max Distance	10 m / 33 ft
Maximum Digital Resolutions	1920x1200
Wide Screen Supported	Yes

---

#### Connector(s)

Connector A	HDMI (19 pin)
Connector B	HDMI (19 pin)

---

#### Special Notes / Requirements

Note	Port 1 is set to have higher priority than port 2 or port 3 when all signals are on. Port 2 is set to have higher priority than port 3 when both signals are on, but Port 1 is off.
------	---



---

**Indicators**

LED Indicators	Two Green for Display Status, and one red for power.
----------------	--

---

**Environmental**

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-65C to 150C (-85F to 302F)
Humidity	10% to 85%RH

---

**Physical Characteristics**

Color	Black
Material	Plastic
Product Length	3.2 in [81 mm]
Product Width	2.2 in [55 mm]
Product Height	1.0 in [25 mm]
Weight of Product	2.4 oz [68 g]

---

**Packaging Information**

Package Length	8.3 in [21 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.6 in [40 mm]
Shipping (Package) Weight	7.6 oz [214 g]

---

**What's in the Box**

Included in Package	3 Port High Speed HDMI Auto Switch
	Remote Control
	IR Extender Cable
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

