

## 2x1 VGA + HDMI to VGA Converter Switch with Priority Switching - 1080p

Product ID: VS221HD2VGA



The VS221HD2VGA VGA & HDMI AutoSwitch lets you connect two distinct A/V sources -- one VGA and one HDMI to the same VGA monitor or projector, and automatically or manually switch between which video source is displayed. This multi-input switch supports video resolution up to 1920x1200 (1080p) and includes mounting hardware for a tidy, professional installation.

The A/V switch features built-in HDMI conversion, enabling you to connect an HDMI as well as a VGA video source to the same VGA display, without the use of additional adapters or scalars. The switch also supports EDID pass-through, EDID copy, and EDID emulation to ensure your HDMI and VGA native resolutions will be maintained between both source connections.

The VS221HD2VGA ensures hassle-free operation with support for priority port selection, enabling you to choose which port should be selected first by sequence. Once the device connected to your specific port is activated, the switch will then automatically select that port.

This A/V switch has been designed with the boardroom and classroom in mind. The VS221HD2VGA features VGA and HDMI inputs to support a wide range of devices, and the built-in converter makes it easy to connect to a display without the use of additional adapters. Plus, priority switching encourages on-the-fly collaboration among students or co-workers, by making it easy to share your projector between multiple source devices.

Please note: Digitally encrypted content from the HDMI video source will not be displayed on the VGA display. If you are looking for a similar device with [%product id="VS221VGA2HD" text="HDMI output"%], please see our [%product id="VS221VGA2HD" text="VS221VGA2HD."%]

If you are looking for a similar device with HDMI output, please see our [%product id="VS221VGA2HD" text="VS221VGA2HD"%]

The VS221VGA2HD is TAA compliant and backed by a StarTech.com 2-year warranty, and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Automatically switch between your set-top box or computer in a home theatre environment
- Share a classroom or conference room projector with VGA and HDMI video sources
- Connect and switch between VGA and HDMI video sources on a test bench, for troubleshooting computers
- Switch between VGA and HDMI video sources on your digital signage display in hospitals, shopping centers, or schools

## Features

- Accommodates both VGA and HDMI input devices in a single switch with VGA output, saving hassle and expense by reducing the need for adapters
- Effortless control with priority port selection
- Supports video resolutions up to 1920x1200 / 1080p
- Supports EDID pass-through, EDID Copy and EDID Emulation
- Mounting hardware included
- Ideal for classroom and boardroom display applications, allowing presenters to connect a wide range of devices

|                     |                             |  |
|---------------------|-----------------------------|--|
| <b>Hardware</b>     | Warranty                    | 2 Years                                      |
|                     | AV Input                    | HDMI   |
|                     | AV Input                    | VGA  |
|                     | Ports                       | 2  |
|                     | AV Output                   | VGA  |
|                     | Audio                       | Yes  |
| <b>Performance</b>  | Maximum Analog Resolutions  | 1920x1200                                    |
|                     |                             | 1920x1200                                    |
|                     | Maximum Digital Resolutions | Supports resolutions up to 1920x1200 / 1080p |
|                     | Supported Resolutions       | Yes  |
|                     | Wide Screen Supported       | 2-channel 3.5mm stereo audio                 |
|                     | Audio Specifications        |  |
| <b>Connector(s)</b> | Connector A                 | VGA (15 pin, High Density D-Sub)             |
|                     | Connector A                 | HDMI (19 pin)                                |
|                     | Connector B                 | VGA (15 pin, High Density D-Sub)             |

**Special Notes / Requirements** Note Digitally encrypted content from the HDMI video source will not be displayed on the VGA display

|                                 |                              |   |
|---------------------------------|------------------------------|---|
| <b>Indicators</b>               | LED Indicators               | VGA Port Selected                         |
|                                 | LED Indicators               | HDMI Port Selected                        |
| <b>Power</b>                    | Power Source                 | AC Adapter Included                       |
|                                 | Input Voltage                | 100 - 240 AC                              |
|                                 | Input Current                | 0.4 A                                     |
|                                 | Output Voltage               | 5 DC                                      |
|                                 | Output Current               | 2 A                                       |
|                                 | Power Consumption (In Watts) | 10  |
| <b>Environmental</b>            | Operating Temperature        | 0C to 40C (32F to 104F)                   |
|                                 | Storage Temperature          | -20C to 60C (-4F to 140F)                 |
|                                 | Humidity                     | 0%~80%                                    |
| <b>Physical Characteristics</b> | Product Length               | 3.3 in [84.000 mm]                        |
|                                 | Product Width                | 2.3 in [59.000 mm]                        |
|                                 | Product Height               | 0.8 in [20.000 mm]                        |
|                                 | Weight of Product            | 6.1 oz [172.000 g]                        |
| <b>Packaging Information</b>    | Package Length               | 9.3 in [2.4 cm]                           |
|                                 | Package Width                | 6.1 in [1.6 cm]                           |
|                                 | Package Height               | 2.6 in [66.000 mm]                        |
|                                 | Shipping (Package) Weight    | 21.2 oz [600.000 g]                       |
| <b>What's in the Box</b>        | Included in Package          | VGA+HDMI to VGA converter switch          |
|                                 | Included in Package          | mounting brackets                         |
|                                 | Included in Package          | universal power adapter (NA, EU, UK, ANZ) |
|                                 | Included in Package          | instruction manual                        |

*\*Product appearance and specifications are subject to change without notice.*