

2X2 HDMI Matrix Switch w/ Automatic and Priority Switching – 1080p

Product ID: VS222HDQ



Save time and hassle by automatically switching between your HDMI audio/video sources, using the VS222HDQ 2X2 HDMI Matrix Switcher. This easy-to-use HDMI Matrix switch ensures seamless transition while switching video and display sources, with EDID copy maintaining your video resolution.

Ensure seamless transition while switching video sources, with EDID copy maintaining native resolution with support for 1080p. Video connection emulation ensures the settings on any connected computers are not disrupted while switching to a different video source.

Save time by connecting two HDMI video source devices to two independent HDMI displays instead of manually connecting individual cables. Mounting hardware is also included for a tidy, professional installation.

Enjoy hassle-free operation with four different switching modes:

Automatic port selection: Enables your most recently activated video source to be displayed automatically.

Priority port selection: Prioritizes input number two above input number one. If the video source connected to input number two is activated that source will be displayed.

Matrix port selection: Independently switch two displays between two video sources.

Manual port selection: Enables you to manually select your HDMI source with easy-to-use front panel buttons.

This product is TAA compliant and backed by a Startech.com 2 warranty with lifetime technical support

Certifications, Reports and Compatibility

Applications

- Connect and switch between two video sources and two displays on a test bench, for troubleshooting computers
- Switch between different video sources on your digital signage display in hospitals, shopping centers, or schools
- Run multimedia presentations with supporting data displayed on another monitor in business conference rooms or at trade shows
- Automatically switch between your Blu-ray player, set top box, or gaming console in a home theatre environment

Features

- Auto switching
- Priority switching
- EDID emulation
- 2x2 Matrix switching
- Support for video resolution up to 1080p
- Built-in manual control console
- Video connection emulation
- Mounting hardware included

Hardware

Warranty	2 Years
AV Input	HDMI
Ports	2
AV Output	HDMI
Cabling	HDMI
Audio	Yes
Rack-Mountable	Yes

Performance

Max Distance	10 m / 33 ft
Maximum Digital Resolutions	1920x1200 / 1080p
Supported Resolutions	1920x1200



1920x1080 (1080p)

1280x720 (720p)

Wide Screen Supported Yes

Audio Specifications 7.1 surround sound

Connector(s)

Connector A HDMI (19 pin)

Connector B HDMI (19 pin)

Indicators

LED Indicators Display #1 - source #1 activated

Display #1 - source #2 activated

Display #2 - source #1 activated

Display #2 - source #2 activated

Power

Power Source AC Adapter Included

Input Voltage 100 - 240 AC

Input Current 0.6 A

Output Voltage 12V DC

Output Current 1.5 A

Plug Type M

Power Consumption (In Watts) 18

Environmental

Operating Temperature 0C to 40C (32F to 104F)

Storage Temperature -20C to 60C (-4F to 140F)

Humidity 0%~80%

Physical Characteristics

Color Black



Material	Aluminum and Plastic
Product Length	6.2 in [15.7 cm]
Product Width	2.6 in [65 mm]
Product Height	0.8 in [20 mm]
Weight of Product	10.2 oz [290 g]

Packaging Information

Package Length	11.5 in [29.2 cm]
Package Width	7.7 in [19.5 cm]
Package Height	2.8 in [72 mm]
Shipping (Package) Weight	19.2 oz [545 g]

What's in the Box

Included in Package	HDMI matrix switch
	remote control
	universal power adapter (NA, EU, UK, AU)
	instruction manual
	mounting kit
	foot pad set

****Product appearance and specifications are subject to change without notice.***

