

## Wall Mount Workstation, Full Motion Sit Stand Desk w/ Height Adjustable VESA Monitor Arm & Keyboard Tray, Ergonomic Wall Mounted Computer Workstation, Single 27"/34" Display - TAA

**Product ID:** WALL-WORKSTATION-S



This Sit-Stand Wall Mount Workstation allows you to create an ergonomic standing desk setup. This is the ideal solution for installations with limited space for a traditional desk, such as offices, labs, clinics, or warehouses. The workstation features a foldable keyboard with an ambidextrous slide-out mousepad tray. The spring-assisted arm allows for height adjustment and lets you alternate between sitting and standing without interrupting your workflow. Adjust your workstation up, down, left or right, to suit the user's ergonomic requirements.

Modify your position with one smooth motion using the built-in handle. Hold and lift the work surface with a range of up to 17.2in (43.8cm) to adjust the workstation's height. You can change the height adjustment tension to suit the user's needs. The VESA (75x75/100x100) monitor mount features an independent height adjustment with a range of up to 4.8in (12.4cm) along the monitor column.

The VESA monitor mount supports one monitor (up to 27" or 34" ultrawide), tilts +35/-5, and rotates up to 360 to accommodate vertical and horizontal monitor orientations.

The workstation can reach up to 37.6in (95.6cm) from the wall when the keyboard tray is extended.

The workstation features a large keyboard tray (17.6x8.1in / 44.9x20.7cm). A retractable mousepad tray (8.6x8.4in / 21.9x21.3cm) slides-out to the left or right to suit the user's needs.

To make the most of the workspace, tuck the workstation away with a slim 13.1in (33.3cm) profile from the wall and free up space when not in use. The articulating arm swivels +/-90, and the keyboard tray folds up to 90. Built-in mouse and handheld scanner holders and cable management solution complement the design.

Combine with CPUWALLMNT to wall mount a computer nearby for a complete workstation solution.

The wall-mounted computer workstation is backed for 2-years, including free lifetime 24/5 multi-lingual technical assistance.

## Certifications, Reports and Compatibility



## Applications

## Features

- **WALL MOUNT WORKSTATION:** Ergonomic sit-stand desk with spring-assisted articulating arm, keyboard tray and retractable mouse tray - VESA compatible mount (75x75 / 100x100) - Monitor capacity up to 17.6lb (8kg) and 27" (or 34" ultrawide)
- **FOLDABLE WORKSTATION:** Tilt 90 and stow away when not in use (13.1"/33.3cm from wall); Adhesive strip secures keyboard - Slide-out left/right mouse tray - Extended arm allows monitor to reach 21.5in (54.8cm) & keyboard tray 37.6in (95.6cm) from wall
- **WIDE RANGE OF MOTION:** Height-adjustable wall-mounted workstation swivels +/-90&deg, arm bends +65/-30&deg (up/down) - Single monitor mount supports +35/-5 tilt, 360 rotation - One-touch height adjustment of the monitor up to 4.9in (12.4cm)
- **WALL MOUNT STANDING DESK:** Adjust your workstation in a single motion using the built-in handle - PC workstation height adjustment range of up to 17.2in (43.6cm) - Add CPUWALLMNT (sold separately) to wall-mount a computer nearby - Adjustment tools included
- **INTUITIVE DESIGN:** Removable mouse tray & wrist rest cover allow for frequent cleaning of all high-touch surfaces, ideal for a shared workstation in an office, clinic, or warehouse - Built-in cable management - Mouse and handheld scanner holders

---

### Hardware

|                           |                  |
|---------------------------|------------------|
| Warranty                  | 2 Years          |
| Wallmountable             | Yes              |
| Cable Management          | Yes              |
| Tools Included            | Yes              |
| Articulating              | Yes              |
| # of Displays Supported   | 1                |
| Mounting Options          | Wall-Mount       |
| Minimum Profile from Wall | 13.1 in [333 mm] |
| VESA Hole Pattern(s)      | 75x75 mm         |

100x100 mm

## Performance

|                                  |                  |
|----------------------------------|------------------|
| Weight Capacity (Per Display)    | 17.6 lb [8 kg]   |
| Weight Capacity of Keyboard Tray | 5.5 lb [2.5 kg]  |
| Maximum Display Size             | 27"              |
|                                  | 34" (21:9)       |
| Fits Curved Display              | No               |
| Fits UltraWide Displays          | Yes              |
| Height Adjustment                | Yes              |
| Maximum Height                   | 36.5 in [926 mm] |
| Minimum Arm Extension            | 14.5 in [369 mm] |
| Maximum Arm Extension            | 21.6 in [548 mm] |
| Display Tilt                     | +35 / -5         |
| Keyboard Tray Tilt               | 0 to 90          |
| Swivel / Pivot                   | +90 / -90        |
| Display Rotation                 | 360              |
| Anti-theft                       | No               |

## Special Notes / Requirements

|      |                                                                            |
|------|----------------------------------------------------------------------------|
| Note | When using ultrawide (21:9) monitors only landscape position is supported. |
|------|----------------------------------------------------------------------------|

## Physical Characteristics

|                     |                    |
|---------------------|--------------------|
| Color               | Silver             |
| Material            | Aluminum and Steel |
| Keyboard Tray Width | 17.7 in [449 mm]   |
| Keyboard Tray Depth | 8.1 in [207 mm]    |

|                   |                   |
|-------------------|-------------------|
| Product Length    | 37.6 in [95.6 cm] |
| Product Width     | 26.3 in [66.8 cm] |
| Product Height    | 36.5 in [92.6 cm] |
| Weight of Product | 19.3 lb [8.8 kg]  |

---

#### Packaging Information

|                           |                   |
|---------------------------|-------------------|
| Package Quantity          | 1                 |
| Package Length            | 16.6 in [42.2 cm] |
| Package Width             | 22.9 in [58.2 cm] |
| Package Height            | 8.8 in [22.4 cm]  |
| Shipping (Package) Weight | 23.4 lb [10.6 kg] |

---

#### What's in the Box

|                     |                        |
|---------------------|------------------------|
| Included in Package | 1 - Monitor Arm        |
|                     | 1 - Keyboard Tray      |
|                     | 1 - Column             |
|                     | 1 - VESA Monitor Mount |
|                     | 1 - Wall Plate         |
|                     | 2 - Adhesive Strips    |
|                     | 4 - Mounting Screws    |
|                     | 4 - Concrete Anchors   |
|                     | 1 - 6mm Hex Key        |
|                     | 1 - 5mm Hex Key        |
|                     | 1 - 2.5mm Hex Key      |
|                     | 1 - M6x8mm Screw       |
|                     | 4 - M4x10 mm Screws    |
|                     | 4 - M6x12mm Screws     |

3 - M6x10mm Screws

1 - M8x30mm Screw

2 - M3x8mm Screws

1 - Socket Driver

1 - Metal Washer

1 - Plastic Washer

1 - User Manual

---

**Warranty  
Information**

Warranty

2 Years

---

*\*Product appearance and specifications are subject to change without notice.*