

2-Post 8U Open Frame Wall Mount Network Rack with Built-in Shelf, Wall Mount Data Rack with Adjustable Depth for AV / Computer / IT Equipment, Small Wall-Mount Server Rack - TAA Compliant

Product ID: WALLSHELF8U



StarTech.com

This wall-mount rack provides 8U of space for mounting your servers or A/V equipment to a wall. The rack also has a built-in shelf to create a sturdy surface for storing equipment that is not rack-mountable.

The wall-mount bracket features an adjustable mounting depth of 12 inches to 18 inches as well as a dual-position 12 in. shelf that can be at either the top or the bottom depending on rack's positioning. These two features allow you to customize both depth and layout to best fit your equipment and cables, ensuring that the rack suits your space.

The 8U rack wall mounting feature allows you to free up desk or floor space -- perfect for your SoHo (small office, home office) environment, server room or any other location with limited space available.

The wall rack is constructed of solid steel to ensure a sturdy and safe mounting solution for your mission-critical equipment and with the wall mounting holes positioned 16" apart, it exactly matches standard drywall construction framework, to ensure simple and secure wall-stud anchoring.

For hassle-free equipment installation, the rack features 10-32 tapped rails, so you can mount your equipment directly to the rail and avoid the hassle of using cage nuts.

The wall-mount rack comes in a flat-packed box to reduce shipping volume, which significantly reduces your costs in shipping while also providing greater protection than offered by pre-assembled racks. Packaged efficiently, you can easily store and transport the rack for deployment at a later date or in a different location than where it's received.

The WALLSHELF8U is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Install networking and telecommunication equipment flush against the wall
- Use in your small office environment where you can't comfortably fit a full-sized rack
- Store frequently used tools on the built-in shelf
- Place equipment that's not rack-mountable on the built-in shelf

Features

- **ADJUSTABLE DEPTH:** 2-Post 8U wall-mount server rack features an adjustable depth of 12" to 18" (30,0cm to 45,7cm) as well as a dual-position 12" shelf that can be installed at the top or the bottom of the rack
- **HASSLE-FREE INSTALLATION:** the wall mount network rack features 10-32 tapped rails for hassle-free IT equipment installation; Directly mount your equipment to the rail without using any cage nuts
- **STURDY AND SAFE:** the open post wall rack is constructed of solid steel to ensure a sturdy and safe mounting solution for your equipment; Wall mounting holes positioned 16" (40cm) apart to match standard NA drywall framework; EIA/ECA-310-E Compliant
- **PERFECT FOR SMALL SPACES:** The wall mounting feature allows you to free up desk or floor space, making the data rack ideal for your small home / office (SoHo) environment, or any other location with limited space available
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this TAA compliant wall mount bracket is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	8U
Special Features	Easy Assembly
	Wall-Mountable
Mounting Rail Profile	L-Shape

	Mounting Hole Types	Threaded Hole
	Industry Standards	EIA/ECA-310-E
Performance		
	Weight Capacity	75.0 lb [34.0 kg]
Physical Characteristics		
	Color	Black
	Construction Material	Steel
Product Measurements		
	Product Length	18.0 in [45.7 cm]
	Product Width	19.0 in [48.3 cm]
	Product Height	17.6 in [44.6 cm]
	Weight of Product	24.5 lb [11.1 kg]
	Maximum Mounting Depth	18.0 in [45.7 cm]
Packaging Information		
	Flat Pack (Assembly Required)	Yes
	Package Length	20.2 in [51.2 cm]
	Package Width	22.0 in [56.0 cm]
	Package Height	2.0 in [5.0 cm]
	Shipping (Package) Weight	26.0 lb [11.8 kg]
What's in the Box		
	Included in Package	1 - back plate
		1 - right bracket
		1 - left bracket
		1 - shelf bracket

2 - adjustable rails

16 - 10-32 x 3/8 screws

24 - 10-32 mounting screws

1 - mounting template

6 - wood screws

1 - instruction manual

****Product appearance and specifications are subject to change without notice.***