

30W USB-C Wall Charger - Portable GaN Charger w/ Power Delivery - 6ft Cable - USB C Power Adapter w/ Fast Charging - USB Type C Wall Charger, USB-C Charger

Produkt-ID: WCH1C30



This USB-C Power Delivery charger features next-generation gallium nitride (GaN) technology. Charge a USB Type-C phone, tablet, or laptop at 30W with this compact and powerful charger.

GaN is a high-performance material used to construct the transistors featured in the newest charging devices. GaN transistors produce less heat, allowing components to be situated closer together, making it possible to manufacture more compact chargers. These new GaN chargers are much smaller than their silicon transistor counterparts of equal power specifications.

This USB-C wall charger is compatible with a vast array of USB Type-C devices such as the MacBook Air, Chromebook, iPad Air / Pro, iPhone, Samsung Galaxy, and Google Pixel. A 6-foot (2-meter) USB-C cable is included. The USB-C AC adapter is compatible with other cable lengths.

The USB Type-C power adapter is compatible with any USB-C Power Delivery device. Maintain optimal charging performance by charging USB-C Power Delivery devices requiring 30W or less.

The USB-C portable charger features multiple forms of protection for your devices such as over-temperature protection, over-current protection, over-voltage protection, and short-circuit protection.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **USB-C GAN CHARGER:** 30 Watt USB-C wall charger with Power Delivery and removable 6.6ft/2m USB C cable; Compact travel adapter (2 oz/58 g); GaN technology produces less heat allowing a smaller size charger with the same power as a standard OEM charger
- **FAST CHARGING:** This portable PD adapter with a detachable USB-C cable (included) supports multi-voltage charging at 5V, 9V, 15V, 20V and up to 30W of power for charging most quick/rapid charging compatible devices
- **COMPATIBILITY:** Compatible with all USB-C enabled laptops, phones, and tablets; MacBook Air, iPhone 15 (Plus/Pro/Max) and up, iPad/iPad Pro, Samsung Galaxy, One Plus, and Google Pixel 6 Pro/6
- **SAFE & RELIABLE:** The USB Type C power wall adapter is built for safe and reliable operation, featuring over voltage, current, and temperature protection; UL Listed components; FCC/ICES certifications; Foldable plugs for transportation and storage
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 30W USB-C charging cube is backed for 2 years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Garantiebestimmungen 2 Years

Ports 1

Steckverbinder

Eingangssteckverbinder 1 - NEMA 1-15 Strom (Nordamerika)

Ausgangssteckverbinder 1 - USB Typ-C (24-polig) Nur USB Power Delivery

Anzeiger

LED-Anzeiger 1 - Blau

Strom

Eingangsspannung 110V-240V AC

Eingangsstrom 1.5 A

Ausgangsspannung 5V DC

9V DC

	15V DC
	20V DC
Ausgangsstrom	3 A
Steckertyp	NEMA 1-15 Power (North America) Plug
Stromverbrauch	30 W
Umgebungsbedingungen	
Betriebstemperatur	0 to 25°C (32 to 77°F)
Lagertemperatur	-20 to 85°C (-4 to 185°F)
Feuchtigkeit	20% bis 90% relative Luftfeuchtigkeit
Physische Eigenschaften	
Farbe	Schiefergrau
Kabellänge	6.6 ft [2 m]
Produktlänge	1.8 in [4.6 cm]
Produktbreite	1.1 in [2.8 cm]
Produkthöhe	1.7 in [4.4 cm]
Produktgewicht	2.0 oz [56.0 g]
Verpackungsinformationen	
Paketmenge	1
Paketlänge	5.0 in [12.8 cm]
Paketbreite	4.6 in [11.8 cm]
Pakethöhe	1.4 in [3.5 cm]
Versandgewicht (Verpackung)	5.9 oz [168.0 g]
Verpackungsinhalt	
Im Paket enthalten	1 - 30W USB-C PD Charger

1 - USB-C Charge Cable

Garantieinformatio
nen

Warranty

2 Jahre

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.