

1000 ft Roll of Blue Plenum CMP Cat 6 Solid UTP Bulk Cable - CMP/FT6 Plenum Fire Rating - ETL Verified - 23 AWG - 1000ft Cat6

Product ID: WIRC6CMPBLU



The WIRC6CMPBLU Cat6 Plenum Bulk Cable meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a durable blue PVC jacket that enables you to color code your network cable runs as needed for a more organized installation.

Constructed of only top quality materials, the WIRC6CMPBLU delivers reliable performance and is backed by our Lifetime Warranty.

This Category 6 cable has been tested for CMP (FT6) plenum-ratings, and is ideal for installation in air plenums, ducts, walls, conduit, ceilings, etc. where CMP fire rating is required.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 23 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

Certifications, Reports and Compatibility

Applications

- Can be used in air ducts and plenums where CMP fire rating is required
- Designed for use with Gigabit networks

Features

- UL Listed CMP/FT6 Plenum Fire Rating
- Foot-marked cable
- ETL Verified
- High quality 23 AWG copper wire
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Constructed with top quality components

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMP Rated (Plenum)

Performance

Cable Rating	CAT6 - 500 MHz
--------------	----------------

Physical Characteristics

Color	Blue
Wire Gauge	23 AWG
Conductor Type	Solid Copper
Cable Length	1000.0 ft [304.9 m]
Product Length	1000.0 ft [304.9 m]
Product Width	0.2 in [6 mm]
Product Height	0.2 in [6 mm]
Weight of Product	33.2 lb [15 kg]

Packaging Information

Package Length	16.7 in [42.5 cm]
Package Width	16.7 in [42.3 cm]



Package Height	9.4 in [23.9 cm]
Shipping (Package) Weight	34.4 lb [15.6 kg]

What's in the Box

Included in Package	1000 ft Roll of Blue CMP Cat 6 Solid UTP Bulk Cable
---------------------	---

**Product appearance and specifications are subject to change without notice.*

