

10/100 VDSL2 Ethernet Extender Kit over Single Pair Wire – 1km

Product ID: 110VDSLEXT



The 110VDSLEXT VDSL Ethernet extender kit lets you span a 10/100 network over extremely long distances (up to 1km) while still maintaining high-speed network connectivity, allowing you to run the connection over standard RJ45 cabling, existing RJ11 phone lines, or any other set of single pair wires. The VDSL (VDSL2) kit is simple to install and provides an out-of-the-box solution as both the Ethernet-VDSL extender and receiver units are included.

A perfect solution for a broad range of applications including connecting isolated user stations within the same building or between separate buildings, or overcoming infrastructure obstacles and distances (e.g. older stone/concrete architecture) where new wiring or wireless may be impossible. The VDSL Ethernet LAN Extender kit helps to eliminate expense by allowing video streaming and data to share the same telephone pair without interference.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Provide ethernet over copper connectivity to a user or network segment that is in an isolated area of a large complex or in another building altogether
- Extend network connectivity to remote areas of stadiums, auditoriums or other venues
- Industrial applications include controlling CNC machinery, polling bar code scanner data, administering process control equipment, and other harsh environment applications
- Monitor and control medical equipment, security keypads/card scanners, point of sale equipment and remote sensor

data, and various other healthcare related network communications

- Remote sensor monitoring for traffic flow management (air traffic control, expressway flow)

Features

- Light in weight and a very compact design
- Supports flow control for Fast Ethernet (pause frame or Back Pressure)
- IEEE 802.1Q VLAN tag transparent
- Allows you the ability to select fixed SNR margin (9 dB) or fixed target data rate
- Supports both symmetric and asymmetric transmission
- Selectable CPE and CO mode via DIP switch

Hardware	Warranty	2 Years
	Industry Standards	IEEE 802.3/802.3u/802.3x10/100 Base-T Auto-Negotiation, Auto-MDI/MDI-X
	Industry Standards	On-board surge protection
		VDSL2 ITU-T G.993.2, VDSL ITU-T G.993.1, and VDSL2/VDSL ITU-T G.997.1 compliant
Performance	Maximum Data Transfer Rate	0m - 100Mbit/s
		300m - 75Mbit/s
	Max Distance	1km - 10Mbit/s
		1 km (0.6 mi)
Connector(s)	Local Unit Connectors	RJ-45
	Remote Unit Connectors	RJ-45
Special Notes / Requirements	Note	You have the ability to use up to four sets over a single Cat5e or Cat6 cable which can be used as separate LAN (or VLAN) connections, or bridged into a trunk line for additional speed/bandwidth over long distances (Up to two sets only over standard Cat5).
Indicators	LED Indicators	LAN: ACT/LNK, 10/100 Mbps, Half/Full Duplex
	LED Indicators	VDSL: Power On/Off, CO/CPE, Idle/Trained/Link
Power	Power Source	2 AC Adapters Included
	Output Voltage	12V DC
Environmental	Operating Temperature	0C to 50C (32F to 122F)
	Storage Temperature	0C to 70C (32F to 158F)
	Humidity	10~90% RH

Physical Characteristics	Color	Black
	Product Length	3.7 in [95 mm]
	Product Width	2.8 in [72 mm]
	Product Height	0.9 in [22 mm]
	Weight of Product	6.1 oz [173 g]

Packaging Information	Package Length	6.0 in [1.5 cm]
	Package Width	7.2 in [1.8 cm]
	Package Height	5.2 in [1.3 cm]
	Shipping (Package) Weight	24.6 oz [696 g]

What's in the Box	Included in Package	Ethernet VDSL Receiver
	Included in Package	Ethernet VDSL Extender
	Included in Package	Instruction Manual
	Included in Package	RJ-45 to VDSL Cable
	Included in Package	Power Adapter

****Product appearance and specifications are subject to change without notice.***

