

USB-C Triple Monitor Docking Station - HDMI/DP Triple 4k USB-C Dock - 5x USB Hub - GbE - 100W PD - Universal Multi Monitor Docking Station - Thunderbolt 3/4 Compatible

**Product ID:** 116E-USBC-DOCK



This USB-C Triple 4K Monitor Docking Station enables wide workstation flexibility, featuring compatibility with USB-C, or Thunderbolt 3/Thunderbolt 4 laptops, and supporting multiple combinations of Ultra HD 4K DisplayPort and HDMI monitors.

This triple-4K docking station uses a combination of its integrated DisplayLink graphics controller and your computer's DP Alt Mode enabled USB-C port to provide three independent 4K displays.

Connect any combination of HDMI and/or DisplayPort monitors to Video Ports 1 and 2 (DisplayLink), at resolutions up to 4K at 60Hz. Connect an HDMI monitor to Video Port 3 (DP Alt-Mode), at resolutions up to 4K at 30Hz. This high-resolution video performance is ideal for detailed graphics applications, enhancing your productivity by expanding the display capabilities of your laptop.

Connect the docking station to your computer's USB 3.2 Gen 2 (10Gbps) Type-C port to provide a wide range of port connectivity, options and features. The docking station features:

- 2x USB-A and 1x USB-C (USB 3.2 Gen 1 5Gbps) ports for USB peripheral devices.
- 1x USB-A and 1x USB-C (USB 3.2 Gen 2 10Gbps) port that supports BC 1.2 with 7.5W (1.5A) for charging tablets and smartphones.
- 1x Gigabit Ethernet port with WoL (Wake-on-LAN) for a wired Local Area Network (LAN) connection.
- 1x 3.5mm 4-position TRRS Audio Jack for a 3.5mm headset.

The USB-C docking station supports 100W USB Power Delivery with the included power adapter. This allows you to charge the connected host device, as well as the devices connected to the BC 1.2 USB charging ports.

For added protection to connected USB devices, the BC 1.2 enabled USB charging ports feature Overcurrent Protection (OCP). OCP prevents USB peripherals from drawing more power than is safely allocated for the port.

Connect the dock to your host computer, using the included 3.3ft (1m) USB-C cable. The docking station supports all major operating systems, including Windows, macOS, ChromeOS, and Ubuntu. This dock was designed for seamless integration with any compatible USB-C equipped device within your organization, including Lenovo X1/Thinkpad P Series, Dell Latitudes/Precision/XPS 15, HP Envy, Surface Laptop 3, and M1 Pro/Max/M2 MacBooks. The dock features a side-facing K-Slot for added security in shared workspaces (e.g., BYOD hoteling/hot-desking).

Developed to improve performance and security, StarTech.com Connectivity Tools is the only software suite on the market that works with a wide range of IT connectivity accessories. The software suite includes:

Advanced Windows Layout Utility: Setup and save custom windows layouts.

Mac Address Pass-Through Utility: Improve network security.


USB Event Monitoring Utility: Track and log connected USB devices.

Wi-Fi Auto Switch Utility: Enable users to quickly access faster network speeds via wired LAN.

For more information and to download the StarTech.com Connectivity Tools application, please visit:  
[www.StarTech.com/Connectivity-Tools](http://www.StarTech.com/Connectivity-Tools)

This product is backed for 3-years by StarTech.com, including free lifetime 24/5 multi-lingual technical assistance.

## Certifications, Reports and Compatibility



## Applications

- Use in laptop hot-desk workstations for hoteling
- Charge your tablets and smartphones from the B.C 1.2 USB ports

## Features

- HIGH-PERFORMANCE TRIPLE 4K VIDEO: USB C Multi Monitor Docking Station features flexible video outputs that enable you to connect two 4K 60Hz HDMI 2.0 and/or DisplayPort 1.2 (DP++) monitors via DisplayLink and a 3rd 4K 30Hz HDMI monitor via DP 1.2 Alt Mode

- **UNIVERSAL COMPATIBILITY:** Compatible with Windows, macOS, ChromeOS & Ubuntu, enabling extended triple displays on USB-C & Thunderbolt 3 and 4 laptops including Apple M1/M2 MacBooks which are not natively capable of driving more than one external display
- **FULL FEATURE DOCK:** 5-Port USB Hub with 3x USB-A (2x 5Gbps, 1x 10Gbps w/BC 1.2 charging) and 2x USB-C (1x 10Gbps w/BC 1.2, 1x 5Gbps) - 100W USB PD - 3.5mm Headset/Audio port and Gigabit Ethernet (WoL) - K Slot - OCP protects devices from power surges
- **100W POWER DELIVERY 3.0:** Power and charge USB-C and Thunderbolt 3/4 laptops and ultrabooks including Lenovo X1/Thinkpad P Series, Dell Latitudes/Precision, XPS 15, HP Envy, Surface Laptop 3 and MacBook - Incl. 3.3ft/1m USB-IF Certified USB-C host cable
- **CONNECTIVITY TOOLS:** Optimize the performance and security of this universal docking station, using the included MAC Address Changer, USB Event Monitoring, Windows Layout and Wi-Fi Auto Switch utilities (available for download)

---

## Hardware

|                      |  |
|----------------------|--|
| Warranty             | 3 Years  |
| 4K Support           | Yes  |
| Fast-Charge Port(s)  | Yes  |
| Displays Supported   | 3  |
| Audio                | Yes  |
| Interface            | USB 3.2 Gen 2 10Gbps                                     |
| Bus Type             | USB 3.2 Gen 2  |
| Compatible Lock Slot | Kensington Standard Slot (K-Slot)                        |
| Industry Standards   | HDMI 2.0   |
|                      | DisplayPort 1.4  |
|                      | USB 3.2 Gen 2 (10Gbps)                                   |
|                      | USB 3.2 Gen 1 (5Gbps)                                    |
|                      | 1000Base-T, 100Base-TX, 10Base-T (IEEE802.3ab compliant) |
| Chipset ID           | DisplayLink - DL-6950-N                                  |
|                      | VIA - VL817C0  |
|                      | Parade - PS176C0   |

---

## Performance

|                             |   |
|-----------------------------|---|
| Maximum Data Transfer Rate  | 10Gbps  |
| Maximum Digital Resolutions | 2x HDMI and/or DisplayPort: 4K (4096 x 2160) 60Hz<br>1x HDMI (via DP Alt Mode): 4K (4096 x 2160) 30Hz |
| Type and Rate               | USB 3.2 Gen 2 - 10 Gbit/s   |
| Supported Charging Outputs  | BC 1.2 (1.5A)   |
| Compatible Networks         | 10/100/1000 Mbps  |
| MTBF                        | 44,877 Hours  |

---

### Connector(s)

|                 |  |
|-----------------|--|
| External Ports  | 3 - HDMI (19 pin)<br>2 - DisplayPort (20 pin)<br>1 - USB 3.2 Type-A (9 Pin, Gen 2, 10Gbps, 7.5W Power)<br>1 - USB 3.2 Gen 2 USB Type-C (Fast-Charge, 24 Pin, 10 Gbps)<br>1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)<br>2 - USB 3.2 Type-A (9 pin, Gen 1, 5Gbps)<br>1 - 3.5 mm Mini-Jack (4 Position)<br>1 - RJ-45 |
| Host Connectors | 1 - USB 3.2 Type-C (24 pin, Gen 2, 10Gbps)   |

---

### Software

|                  |   |
|------------------|---|
| OS Compatibility | Windows 7, 8, 8.1, 10, 11<br>>macOS 10.11 to 10.12, 10.14 to 10.15, 11.0, 12.0, 13.0, 14.0<br>>Android<br>>Linux 3.5.x and up - <i>LTS Versions only</i><br>>ChromeOS |
|------------------|---|

---

### Special Notes / Requirements

|                               |   |
|-------------------------------|---|
| System and Cable Requirements | A host device with an available USB-C port (to ensure full adapter functionality, the host device's USB-C port must support USB Power Delivery 2.0 and DP alt mode).  |
| Note                          | Not all USB-C ports support the full functionality of the USB Type-C standard. Ensure your host device's USB-C port supports USB Power Delivery and DP alt mode.<br><br>A 4K-capable display is required to achieve 4096 x 2160p/3840 x |

2160p resolution.

A 4K-capable computer is required to achieve 3840 x 2160p resolution (4K is also known as 4K x 2K) on the DP Alt-Mode HDMI port.

USB 3.2 Gen 1 (5Gbps) is also known as USB 3.1 Gen 1 (5Gbps) and USB 3.0 (5Gbps).

---

**Indicators**

|                |                       |
|----------------|-----------------------|
| LED Indicators | 1 - Power LED (white) |
|----------------|-----------------------|

---

**Power**

|                              |                     |
|------------------------------|---------------------|
| Power Source                 | AC Adapter Included |
| Power Delivery               | 100W                |
| Input Voltage                | 100 - 240 AC        |
| Input Current                | 2.5 A               |
| Output Voltage               | 24 DC               |
| Output Current               | 5.41 A              |
| Center Tip Polarity          | Positive            |
| Plug Type                    | M                   |
| Power Consumption (In Watts) | 15W                 |

---

**Environmental**

|                       |                           |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 70C (32F to 158F)   |
| Storage Temperature   | -10C to 55C (14F to 131F) |
| Humidity              | 0~85% RH (Non-condensing) |

---

**Physical Characteristics**

|                |                  |
|----------------|------------------|
| Color          | Space Gray       |
| Material       | Plastic          |
| Product Length | 7.5 in [19.0 cm] |
| Product Width  | 3.3 in [8.5 cm]  |

|                   |                   |
|-------------------|-------------------|
| Product Height    | 1.2 in [3.0 cm]   |
| Weight of Product | 12.4 oz [350.0 g] |

---

**Packaging Information**

|                           |                  |
|---------------------------|------------------|
| Package Length            | 9.8 in [25.0 cm] |
| Package Width             | 8.1 in [20.5 cm] |
| Package Height            | 2.0 in [5.0 cm]  |
| Shipping (Package) Weight | 2.4 lb [1.1 kg]  |

---

**What's in the Box**

|                     |                                 |
|---------------------|---------------------------------|
| Included in Package | 1 - USB-C Docking Station       |
|                     | 1 - 3 ft [1 m] USB-C Host Cable |
|                     | 1 - Power Adapter (EU)          |
|                     | 1 - Quick-Start Guide           |

---

***\*Product appearance and specifications are subject to change without notice.***