


6 ft 1394b 9 Pin to 9 Pin FireWire 800 Cable M/M

Product ID: 1394_99_6



If your computer's equipped with FireWire 800, you're obviously passionate about speed and performance. Make sure you get the most out of FireWire 800 with quality cables from StarTech.com

This 9-pin 1394b cable will keep your high-bandwidth video or graphic applications moving data at up to 800 Mbps - enough for demanding high-speed digital storage and serious video capture.

StarTech.com FireWire 800 cables come with the highest quality shielding to protect your high speed data connections, and are backed by our lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Ideal for Mass storage, Digital Video (DV), Digital Audio, Digital Cameras, Printers, Scanners, Home entertainment and other Networking products
- Connect multiple FireWire 800(1394b) compliant devices together

Features

- Fast data transfer rate of up to 800 Mbits/sec
- Hot Pluggable feature allows swapping of live devices without turning off your computer
- Compliant with FireWire800 and 1394b standards
- Compatible with all 1394b PC FireWire, Apple FireWire, and Sony iLink devices

- Supports a daisy-chain of up to 63 fireWire devices
- 9-pin cable draws power from FireWire bus
- Highest quality shielding protects from EMI (electromagnetic interference) noise
- Twisted Pair Construction

Hardware

Warranty	Lifetime
Industry Standards	FireWire 800, 1394b

Connector(s)

Connector A	FireWire 800 (9 pin, IEEE 1394b)
Connector B	FireWire 800 (9 pin, IEEE 1394b)

Physical Characteristics

Color	Black
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Weight of Product	2.5 oz [70.8 g]

Packaging Information

Package Length	7.8 in [19.9 cm]
Package Width	0.5 in [13 mm]
Package Height	8.3 in [21.1 cm]
Shipping (Package) Weight	2.5 oz [71.8 g]

What's in the Box

Included in Package	6 ft 1394b 9 Pin to 9 Pin FireWire 800 Cable M/M
---------------------	--

**Product appearance and specifications are subject to change without notice.*

