

12U Adjustable 4 Post Server Equipment Open Frame Rack Cabinet

Product ID: 4POSTRACK12



The 4POSTRACK12 12U Adjustable 4 Post Server Equipment Open Frame Rack Cabinet provides a durable, open air housing for rackmount servers and networking equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The equipment rack/cabinet features heavy gauge mounting rails to ensure a stable installation platform and adjustable posts for flexible installation. The 12U open frame rack is compliant with EIA-RS-310C standards, offering a universal design that's compatible with equipment from popular manufacturers. Plus, the equipment rack is flat-packed, reducing shipping costs and simplifying handling and assembly.

For added versatility, StarTech.com offers an optional 4pc Caster Kit (4POSTCASTER) that can be installed on the bottom of the 12U server rack, making it easier to re-position the cabinet/rack as needed for future uses.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Perfect solution for Technology shops and repair centers with limited space and mountable equipment
- Suitable for rackmount equipment where security at the rack level is not required

- Audio/Video editing room, radio or television studio broadcast rackmount equipment
- Great for satellite offices, and retail locations where a small amount of server equipment is setup
- Useful for point of sale applications, specifically mounting equipment under the check-out counter
- Mounting equipment under a desk/workspace

Features

- Store your servers, network and telecommunications equipment in this 12U open-frame rack
- 12U Open Frame Rack with a weight capacity of 1000 lb (452.5 kg)
- TAA compliant for GSA Schedule purchases
- Flat packed for easy shipping
- Pre-drilled base and unobstructed ventilation
- Heavy gauge adjustable mounting rails ensure broad equipment compatibility

Hardware

Warranty	Lifetime
Wallmountable	No
Rack Type	4-Post
Frame Type	Open Frame
U Height	12U
Special Features	Adjustable Mounting Rails
	Base Plate with Floor-Anchoring Holes
	Casters (Optional)
	Easy Assembly
Mounting Rail Profile	C-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	997.7 lb [452.5 kg]
-----------------	---------------------

Physical Characteristics

Color	Black
Construction Material	Steel

Product Measurements

Product Length	31.5 in [80.0 cm]
Product Width	22.5 in [57.2 cm]
Product Height	25.5 in [64.8 cm]
Weight of Product	63.7 lb [28.9 kg]
Maximum Mounting Depth	39.4 in [100 cm]
Minimum Mounting Depth	18.3 in [46.5 cm]
Product Height with Casters	28.3 in [71.9 cm]

Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	27.8 in [70.5 cm]
Package Width	25.4 in [64.4 cm]
Package Height	6.7 in [17.0 cm]
Shipping (Package) Weight	69.9 lb [31.7 kg]

What's in the Box

Included in Package	1 - 12 U Open Rack
	1 - Assembly Kit (Screw, Hex Key, Caps)
	32 - M5 Screws
	32 - M5 Cage Nuts
	1 - Assembly Instructions

****Product appearance and specifications are subject to change without notice.***