

6ft (1.8m) Hospital-Grade Extension Cord, Green Dot Medical Power Cable, NEMA 5-15P to NEMA 5-15R, 13A 125V, 16AWG, TAA Compliant, UL Listed

Produkt-ID: 231B-660H-POWER-CORD



#### The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

## Zertifikate Berichte und Kompatibilität



## Anwendungen

- Ideal for use in hospitals and medical environments
- Extend a power connection in a hospital or medical setting
- Green dot marking is UL Listed for guaranteed safety and durability
- Green Dot medical power cable for optimal safety and durability

## Merkmale

- **HOSPITAL-GRADE POWER CORD:** 6ft (1.8m) 16AWG Green Dot Power Extension Cord with NEMA 5-15P to NEMA 5-15R connector is safe for hospitals and medical environments; Easy Grip molding for safe handling and frequent use; Indoor use; Rated to carry 125V at 13A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed with Green Dot indicator for use in hospitals and medical settings; VW-1 Fire Rated cable w/molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 6ft (1.8m); TAA Compliant; NEMA 5-15P to NEMA 5-15R; 16AWG; 125V 13A (Max); Jacket Rating: SJT; Color: Gray; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.33in (8.5mm)
- **COMPATIBILITY:** NEMA 5-15P plug works with North American electrical outlets; Extend a 3-prong power cable connection, or safely connect hospital or medical equipment to a wall outlet or PDU
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this hospital-grade extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 3

Typ der PVC  
Kabelummantelung

Feuerwiderstandsklass Klasse VW-1

e

---

Steckverbinder

Steckverbinder A 1 - NEMA 5-15 Strom (Nordamerika)

Steckverbinder B 1 - NEMA 5-15 Strom (Nordamerika)

---

Strom

Eingangsspannung 125V AC

Eingangsstrom 13A

Ausgangsstrom 13A

---

Umgebungsbedingungen

Betriebstemperatur -20° to 105°C (-4° to 221°F)

Lagertemperatur -20° to 105°C (-4° to 221°F)

Feuchtigkeit 0% to 65% RH

---

Physische Eigenschaften

Farbe Grau

Drahtstärke 16 AWG

Kabellänge 6.0 ft [1.8 m]

Außendurchmesser des Kabels 0.3 in [8.5 mm]

Produktlänge 6.0 ft [1.8 m]

Produktbreite 1.1 in [2.7 cm]

Produkthöhe 1.3 in [3.4 cm]

Produktgewicht 10.3 oz [292.0 g]

---

Verpackungsinformationen

Paketlänge 8.0 in [20.2 cm]

Paketbreite 3.1 in [8.0 cm]

Pakethöhe 2.6 in [6.5 cm]

Versandgewicht 10.7 oz [304.0 g]  
(Verpackung)

---

Verpackungsinhalt

Im Paket enthalten 1 - 1,8m Hospital-Grade Netzkabel Verlängerung

---

Garantieinformatio  
nen

Warranty Lifetime

---

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.