


6ft (1.8m) Hospital-Grade Extension Cord, Green Dot Medical Power Cable, NEMA 5-15P to NEMA 5-15R, 13A 125V, 16AWG, TAA Compliant, UL Listed





The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility











Applications

- Ideal for use in hospitals and medical environments
- Extend a power connection in a hospital or medical setting
- Green dot marking is UL Listed for guaranteed safety and durability
- Green Dot medical power cable for optimal safety and durability

Connector A

Features

- HOSPITAL-GRADE POWER CORD: 6ft (1.8m) 16AWG Green Dot Power Extension Cord with NEMA 5-15P to NEMA 5-15R connector is safe for hospitals and medical environments; Easy Grip molding for safe handling and frequent use; Indoor use; Rated to carry 125V at 13A
- BUILT FOR PERFORMANCE AND SAFETY: UL Listed with Green Dot indicator for use in hospitals and medical settings; VW-1 Fire Rated cable w/molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- SPECS: 6ft (1.8m); TAA Compliant; NEMA 5-15P to NEMA 5-15R; 16AWG; 125V 13A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.33in (8.5mm)
- COMPATIBILITY: NEMA 5-15P plug works with North American electrical outlets; Extend a 3-prong power cable connection, or safely connect hospital or medical equipment to a wall outlet or PDU
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this hospital-grade extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware		
	Warranty	Lifetime
	Number of Conductors	3
	Cable Jacket Material	PVC
	Fire Rating	VW-1 Rated
	Cable Type	SJT
Connector(s)		

1 - NEMA 5-15 Power (North America)





	Connector B	1 - NEMA 5-15 Power (North America)
Power		
	Input Voltage	125V AC
	Input Current	13A
	Output Current	13A
Environmental		
	Operating Temperature	-20 to 105C (-4 to 221F)
	Storage Temperature	-20 to 105C (-4 to 221F)
	Humidity	0% to 65% RH
Physical Characteristics		
	Color	Gray
	Wire Gauge	16 AWG
	Cable Length	6.0 ft [1.8 m]
	Cable OD	0.3 in [8.5 mm]
	Product Length	6.0 ft [1.8 m]
	Product Width	1.1 in [2.7 cm]
	Product Height	1.3 in [3.4 cm]
	Weight of Product	0.0 oz [0.0 g]
Packaging Information		
	Package Length	5.7 in [14.5 cm]
	Package Width	11.6 in [29.5 cm]
	Package Height	2.8 in [7.0 cm]
	Shipping (Package) Weight	10.6 oz [300.0 g]
What's in the Box	Included in Package	1 - 6ft Hospital-Grade Power Extension Cord



*Product appearance and specifications are subject to change without notice.