

## Refurbished 15U 19in Black Server Rack Cabinet with Fans

**Product ID:** 2636CABINETR



Refurbished cabinets may have minor scratches and dents.

This Refurbished 15U, 36 in (depth) cabinet features a plexiglass front door, full steel design, and three-fan filtered ventilation helping to keep your servers and other critical equipment cool and protected.

The server equipment cabinet/rack is black, making an attractive addition to your server room, and to ensure maximum versatility, the rack/cabinet includes casters, making it easier to position server equipment as needed.

Every refurbished server rack includes complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty,.

## Certifications, Reports and Compatibility

### Applications

- Perfect solution for Technology shops and repair centers with limited space and mountable equipment where security is required
- Ideal for rack mount servers, KVM switches, networking equipment and cabinet consoles
- Audio/Video editing room, radio or television studio broadcast rackmount equipment
- A great solution for the college/university classroom, where only limited rackmount equipment is needed, but security is still important

### Features

- Extruded aluminum construction provides rounded corners and edges for an attractive appearance

- Fully forward/back adjustable mounting rails inside cabinet
- Front and back doors are removable and can be switched to open left or right
- Rolling casters provide full mobility
- Three (3) roof-mounted fans exhaust up to 300 CFM of air
- Many accessory options available like mounting shelves, keyboard drawers, storage drawers, sliding shelves, front blanking plates, etc.
- Comes fully assembled
- Includes (3) 5" ball bearing AC fans moving up to 300 CFM of air, air filter and adjustable levelers at each corner
- Also comes with front flip-up stabilizers, removable smoked acrylic front door with 2 keys, removable rear door and 50 Philips-head mounting screws

---

#### Hardware

Warranty	None
Wallmountable	No
Rack Type	4-Post
Frame Type	Enclosed Cabinet
U Height	15U
Special Features	Adjustable Mounting Rails Built-in Cable Management Casters (Included) Leveling Feet Ships Fully Assembled
Mounting Rail Profile	L-Shape
Fan Options	Three Fans Included: 120 mm
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

#### Performance

Airflow Rate	82 CFM
--------------	--------



Audible Noise	38 dBA @ 1 Meter
Weight Capacity (Stationary)	2210.0 lb [1000 kg]

---

**Physical Characteristics**

Color	Black
Front Door Construction	Steel with Glass/Acrylic Window
Front Door Features	Secure Key Lock with Reversible and Removable Front Door
Side Panel Construction	Steel
Rear Door Construction	Steel
Rear Door Features	Secure Key Lock with Reversible and Removable Back Door

---

**Product Measurements**

Internal Width	21.9 in [55.6 cm]
Internal Depth	33.9 in [86 cm]
Product Length	35.4 in [90.0 cm]
Product Width	22.0 in [55.9 cm]
Product Height	30.1 in [76.5 cm]
Weight of Product	136.3 lb [61.7 kg]
Maximum Mounting Depth	29.3 in [74.5 cm]
Minimum Mounting Depth	13.4 in [34 cm]
Product Height with Casters	33.2 in [84.3 cm]

---

**Packaging Information**

Flat Pack (Assembly Required)	No
Package Length	36.1 in [91.8 cm]
Package Width	23.3 in [59.3 cm]



Package Height	39.3 in [99.7 cm]
Shipping (Package) Weight	144.4 lb [65.3 kg]

---

**What's in the Box**

Included in Package	26X36X19 Inch 15U Cabinet Equipment Rack
	Bag of screws, fasteners and keys

---

***\*Product appearance and specifications are subject to change without notice.***

