

12ft (3.6m) Heavy Duty Power Cord, NEMA 5-15P to Locking C13 AC Power Cable, 15A 125V, 14AWG, Replacement Computer Power Cord, TAA Compliant, UL Listed

Produkt-ID: 27LC-4B00-POWER-CORD



#### The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

## Zertifikate Berichte und Kompatibilität



## Anwendungen

- Locking C13 connector hinders accidental power disconnection
- Connect a computer, display, or laptop power supply to a wall outlet or PDU

## Merkmale

- HEAVY DUTY AC POWER CORD: 12ft (3.66m) 14AWG Universal Power Cord with NEMA 5-15P to Locking IEC 60320 C13 connector is suitable for workstations/home office or high-power rack mounted equipment such as servers and PDUs; Indoor use; Up to 125V at 15A
- BUILT FOR PERFORMANCE AND SAFETY: UL Listed; Locking C13 connector prevents accidental disconnection; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- SPECS: 12ft (3.66m); TAA Compliant; NEMA 5-15P to Locking IEC 60320 C13; 14AWG; 125V 15A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.36in (9.3mm)
- COMPATIBILITY: NEMA 5-15P plug works with North American electrical outlets; IEC C13 connector works with most computers, monitors, and displays; Replacement PC power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

---

## Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 3

Steckverbinderplatten Nickel

Typ der PVC  
Kabelummantelung

Feuerwiderstandsklass Klasse VW-1  
e

Kabeltyp	SJT
<hr/>	
Leistung	
Max. Kabellänge	
	12.0 ft [3.7 m]
<hr/>	
Steckverbinder	
Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	1 - IEC 60320 C13 Strom
<hr/>	
Strom	
Eingangsspannung	125 AC
Eingangsstrom	15A
<hr/>	
Umgebungsbedingungen	
Betriebstemperatur	-20° to 105°C (-4° to 221°F)
Lagertemperatur	-20° to 105°C (-4° to 221°F)
Feuchtigkeit	0% to 65% RH
<hr/>	
Physische Eigenschaften	
Farbe	Schwarz
Steckverbinderart	Gerade
Drahtstärke	14 AWG
Kabellänge	12.0 ft [3.7 m]
Außendurchmesser des Kabels	0.4 in [9.3 mm]
Produktlänge	12.0 ft [3.7 m]
Produktbreite	1.2 in [2.9 cm]
Produkthöhe	1.0 in [2.6 cm]
Produktgewicht	1.2 lb [0.6 kg]
<hr/>	
Verpackungsinformationen	

Paketlänge 12.6 in [32.0 cm]

Paketbreite 4.4 in [11.2 cm]

Pakethöhe 1.9 in [4.9 cm]

Versandgewicht  
(Verpackung) 1.3 lb [0.6 kg]

---

Verpackungsinhalt

Im Paket enthalten 1 - 4m NEMA 5-15P auf C13 Netzkabel

---

Garantieinformatio  
nen

Warranty Lifetime

---

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.

