

## 41U Rack Enclosure Server Cabinet - 32 in. Deep - Built-in Fans

**Product ID:** 7236CABINET



This 41U 36in Black Server Rack Cabinet offers a lockable, dust-reduced environment for rackmount servers and network equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

With exterior dimensions of H 75.5in x W22in x D35.5in (cabinet only), this sturdy space-saving unit is made from extruded aluminum for an appealing appearance. A standard lockable smoked plexiglass (see-through) front door and solid aluminum rear door provide quick access to installed equipment.

The internal front and rear mounting rails are spaced to accept standard 19in rackmount devices and are completely depth adjustable as to be able to fit virtually any piece of equipment that is less than 33in deep. A standard roof-mounted triple motor AC fan unit and high-flow air filter below the rear door provide up to 300 CFM of bottom to top air flow through the cabinet, removing the heat produced by the enclosed equipment.

In addition to the standard equipment that are options on most other cabinets, the StarRack Cabinet also has a full complement of optional accessories like fixed shelving, storage drawers, keyboard drawers, front panel spacer plates, and slide-out shelves.

## Certifications, Reports and Compatibility

## Applications

## Features

- Extruded aluminum construction provides rounded corners and edges for an attractive appearance
- Fully forward/back adjustable mounting rails inside cabinet

- Front and back doors are removable and can be switched to open left or right
- Rolling casters provide full mobility
- Three (3) roof-mounted fans exhaust up to 300 CFM of air
- Many accessory options available like mounting shelves, keyboard drawers, storage drawers, sliding shelves, front blanking plates, etc.
- Comes fully assembled
- Includes (3) 5" ball bearing AC fans moving up to 300 CFM of air, air filter and adjustable levelers at each corner
- Also comes with front flip-up stabilizers, removable smoked acrylic front door with 2 keys, removable rear door and 50 Philips-head mounting screws
- TAA compliant for GSA Schedule purchases

---


#### Hardware

Warranty	Lifetime
Wallmountable	No
Rack Type	4-Post
Frame Type	Enclosed Cabinet
U Height	41U
Special Features	Adjustable Mounting Rails
	Built-in Cable Management
	Leveling Feet
	Ships Fully Assembled
	Casters (Included)
Mounting Rail Profile	L-Shape
Fan Options	Three Fans Included: 120 mm
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

#### Performance

Airflow Rate	82 CFM
--------------	--------



Audible Noise	38 dBA @ 1 Meter
Weight Capacity (Stationary)	2210.0 lb [1000 kg]

---

### Physical Characteristics

Color	Black
Front Door Construction	Steel with Glass Window
Front Door Features	Secure Key Lock with Reversible and Removable Front Door
Side Panel Construction	Steel
Rear Door Construction	Steel
Rear Door Features	Secure Key Lock with Reversible and Removable Back Door

---

### Product Measurements

Internal Width	21.8 in [55.4 cm]
Internal Depth	35.0 in [89 cm]
Product Length	35.4 in [90 cm]
Product Width	22.0 in [56 cm]
Product Height	6.3 ft [1.9 m]
Weight of Product	200.5 lb [90.7 kg]
Maximum Mounting Depth	32.3 in [82 cm]
Minimum Mounting Depth	14.2 in [36 cm]
Product Height with Casters	6.6 ft [2.0 m]

---

### Packaging Information

Flat Pack (Assembly Required)	No
Package Length	36.4 in [92.4 cm]
Package Width	23.1 in [58.6 cm]



Package Height	7.0 ft [2.1 m]
Shipping (Package) Weight	218.5 lb [98.9 kg]

---

**What's in the Box**

Included in Package	H72"xW19"xD36" 41U Cabinet Equipment Rack
	Bag of screws, fasteners and keys
	M5 Cage Nuts

---

***\*Product appearance and specifications are subject to change without notice.***

