

1ft (30cm) Power Extension Cord, C14 to C13 PDU Power Cord, 10A 250V, 18AWG, Black Extension Cable, AC Power Cable for PDU/Power Supply, TAA Compliant, UL Listed

**Product ID:** 8713-8100-POWER-CORD



The IT Pro's Choice

StarTech.com power cables are designed for IT Pro applications and requirements, including standard and heavy-duty power cords, extension cords, medical-grade cords, splitter and passthrough cables. Performance, safety and reliability are ensured by our in-house and third-party testing labs.

StarTech.com offers an extensive range of options in various lengths, connector ends, jacket types and wire gauges.

- Certified for performance and safety: Made from UL listed components to meet UL62 & UL817
- Environmental safety and compliance with REACH and RoHS.
- 100% copper wiring tested for continuity and conductivity ensuring maximum performance and reliability.
- Temperature chamber tested to ensure cable performs to environmental and jacket rating

Backed for life by StarTech.com with 24-hour, five day-a-week support from qualified Technical Advisor and our IT Pro community forums, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

## Certifications, Reports and Compatibility



## Applications

- Extend a monitor, scanner, printer, or PC power cord by an additional 1 ft
- Extend a power connection from a crowded PDU for more convenient access

## Features

- **AC POWER CORD:** 1ft (30cm) 18AWG power supply extension cable with IEC 60320 C14 to C13 connectors is suitable for workstations/home office or rack mounted equipment; Extend a C13 power cord to a power supply or PDU; Indoor use; Rated to carry 250V at 10A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed; VW-1 Fire Rated cable with fully molded strain reliefs for durability; 3-conductor power cable made with 100% copper wire; Available in other lengths
- **SPECS:** 1ft (30cm); TAA Compliant; IEC 60320 C14 to IEC 60320 C13; 18AWG; 250V 10A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.3in (7.8mm)
- **COMPATIBILITY:** PC Power Cord IEC 60320 C14 works with North American PDUs and cables; IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more; Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C14 to C13 power cord is available in other lengths

---

### Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

---

### Performance

Maximum Cable Length	1.0 ft [0.3 m]
----------------------	----------------

---

### Connector(s)

Connector A	1 - IEC 60320 C14 Power
Connector B	1 - IEC 60320 C13 Power

---

### Power

Input Voltage	250 AC
---------------	--------

Input Current	10A
---------------	-----

---

**Environmental**

Operating Temperature	-20 to 105C (-4 to 221F)
-----------------------	--------------------------

Storage Temperature	-20 to 105C (-4 to 221F)
---------------------	--------------------------

Humidity	0% to 65% RH
----------	--------------

---

**Physical Characteristics**

Color	Black
-------	-------

Connector Style	Straight
-----------------	----------

Wire Gauge	18 AWG
------------	--------

Cable Length	1.0 ft [0.3 m]
--------------	----------------

Cable OD	0.3 in [7.8 mm]
----------	-----------------

Product Length	12.0 in [30.5 cm]
----------------	-------------------

Product Width	1.1 in [2.9 cm]
---------------	-----------------

Product Height	0.8 in [2.1 cm]
----------------	-----------------

Weight of Product	0.0 oz [0.0 g]
-------------------	----------------

---

**Packaging Information**

Package Length	5.7 in [14.5 cm]
----------------	------------------

Package Width	11.4 in [29.0 cm]
---------------	-------------------

Package Height	0.8 in [2.1 cm]
----------------	-----------------

Shipping (Package) Weight	2.5 oz [72.0 g]
---------------------------	-----------------

---

**What's in the Box**

Included in Package	1 - 1ft C14 to C13 Power Extension Cord
---------------------	---

---

*\*Product appearance and specifications are subject to change without notice.*