

2ft (60cm) Power Extension Cord, C14 to C13 PDU Power Cord, 10A 250V, 18AWG, Black Extension Cable, AC Power Cable for PDU/Power Supply, TAA Compliant, UL Listed

Produkt-ID: 8713-8200-POWER-CORD



The IT Pro's Choice

StarTech.com power cables are designed for IT Pro applications and requirements, including standard and heavy-duty power cords, extension cords, medical-grade cords, splitter and passthrough cables. Performance, safety and reliability are ensured by our in-house and third-party testing labs.

StarTech.com offers an extensive range of options in various lengths, connector ends, jacket types and wire gauges.

- Certified for performance and safety: Made from UL listed components to meet UL62 & UL817
- Environmental safety and compliance with REACH and RoHS.
- 100% copper wiring tested for continuity and conductivity ensuring maximum performance and reliability.
- Temperature chamber tested to ensure cable performs to environmental and jacket rating

Backed for life by StarTech.com with 24-hour, five day-a-week support from qualified Technical Advisor and our IT Pro community forums, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Extend a monitor, scanner, printer, or PC power cord by an additional 2ft
- Extend a power connection from a crowded PDU for more convenient access

Merkmale

- **AC POWER CORD:** 2ft (60cm) 18AWG power supply extension cable with IEC 60320 C14 to C13 connectors is suitable for workstations/home office or rack mounted equipment; Extend a C13 power cord to a power supply or PDU; Indoor use; Rated to carry 250V at 10A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed; VW-1 Fired Rated cable with fully molded strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 2ft (60cm); TAA Compliant; IEC 60320 C14 to IEC 60320 C13; 18AWG; 250V 10A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.3in (7.8mm)
- **COMPATIBILITY:** PC Power Cord IEC 60320 C14 works with North American PDUs and cables; IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more; Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C14 to C13 power cord is available in other lengths

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	PVC
Feuerwiderstandssklasse	Klasse VW-1e
Kabeltyp	SJT

Leistung		
	Max. Kabellänge	2.0 ft [0.6 m]
Steckverbinder		
	Steckverbinder A	1 - IEC 60320 C14 Strom
	Steckverbinder B	1 - IEC 60320 C13 Strom
Strom		
	Eingangsspannung	250 AC
	Eingangsstrom	10A
Umgebungsbedingungen		
	Betriebstemperatur	-20° to 105°C (-4° to 221°F)
	Lagertemperatur	-20° to 105°C (-4° to 221°F)
	Feuchtigkeit	0% to 65% RH
Physische Eigenschaften		
	Farbe	Schwarz
	Drahtstärke	18 AWG
	Kabellänge	2.0 ft [0.6 m]
	Außendurchmesser des Kabels	0.3 in [7.8 mm]
	Produktlänge	24.0 in [61.0 cm]
	Produktbreite	1.1 in [2.9 cm]
	Produkthöhe	0.8 in [2.1 cm]
	Produktgewicht	3.2 oz [92.0 g]
Verpackungsinformationen		
	Paketlänge	8.2 in [20.8 cm]
	Paketbreite	3.3 in [8.4 cm]

Pakethöhe 1.4 in [3.6 cm]

Versandgewicht
(Verpackung) 3.5 oz [98.0 g]

Verpackungsinhalt

Im Paket enthalten 1 - 60cm C14 auf C13 Stromkabel Verlängerung

Garantieinformationen

Warranty Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.