

6ft (1.8m) Heavy Duty Power Cord, Right Angle C14 to C13, PDU Power Cord, 15A 250V, 14AWG, Heavy Gauge Power Cable, TAA Compliant, UL Listed

Produkt-ID: 8745-4600-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Extend a monitor, scanner, printer, or PC power cord by an additional 6ft
- Angled C14 connector saves space in crowded installations

Merkmale

- **HEAVY DUTY POWER CORD:** 6ft power supply cable with Right Angle IEC 60320 C14 to Straight C13 connector connects neatly to a power supply or a PDU; 90-degree C14 connector enables convenient access in tight spaces; Rated to carry 250V at 15A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 6ft (1.83m); TAA Compliant; Right Angle IEC 60320 C14 to IEC 60320 C13; 14AWG; 250V 15A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.36in (9.3mm); Indoor use
- **COMPATIBILITY:** PC Power Cord IEC 60320 C14 connector works with North American PDUs and cables; IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more; Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C14 to C13 power cord is available in other lengths

Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 3

Steckverbinderplatten Nickel

Typ der PVC
Kabelummantelung

Feuerwiderstandsklass Klasse VW-1
e

Kabeltyp	SJT	
<hr/>		
Leistung	Max. Kabellänge	6.0 ft [1.8 m]
<hr/>		
Steckverbinder	Steckverbinder A	1 - IEC 60320 C14 Strom
	Steckverbinder B	1 - IEC 60320 C13 Strom
<hr/>		
Strom	Eingangsspannung	250 AC
	Eingangsstrom	15A
<hr/>		
Umgebungsbedingungen	Betriebstemperatur	-20° to 105°C (-4° to 221°F)
	Lagertemperatur	-20° to 105°C (-4° to 221°F)
	Feuchtigkeit	0% to 65% RH
<hr/>		
Physische Eigenschaften	Farbe	Schwarz
	Drahtstärke	14 AWG
	Kabellänge	6.0 ft [1.8 m]
	Außendurchmesser des Kabels	0.4 in [9.3 mm]
	Produktlänge	6.0 ft [1.8 m]
	Produktbreite	1.7 in [4.4 cm]
	Produkthöhe	0.8 in [2.1 cm]
	Produktgewicht	10.7 oz [302.0 g]
<hr/>		
Verpackungsinformationen	Paketlänge	9.7 in [24.7 cm]

Paketbreite	3.7 in [9.4 cm]
Pakethöhe	1.9 in [4.9 cm]
Versandgewicht (Verpackung)	10.8 oz [306.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 1,8 m C13 auf Rechtwinkliges C14 Hochleistungs-Verlängerungskabel
--------------------	--

Garantieinformatio
nen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.

