

4ft (1.2m) Power Extension Cord, PDU Style C14 to Locking C13, PDU Power Cord, 10A 250V, 18AWG, Power Extension Cable, TAA Compliant, UL Listed

Product ID: 87L3-8400-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility











Applications

- Locking C13 connector avoids accidental power disconnection
- Extend a monitor, scanner, printer, or PC power cord by an additional 4ft

Features

Connector(s)

- AC POWER CORD: 4ft (1.22m) power supply extension cable with IEC 60320 C14 to Locking C13 connector is suitable for workstations or rackmount equipment; Securely connect devices to a PDU or extend a C13 power cable; Indoor use; Rated to carry 250V at 10A
- BUILT FOR PERFORMANCE AND SAFETY: UL Listed; Locking C13 connector prevents accidental disconnection; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- SPECS: 4ft (1.22m); TAA Compliant; IEC 60320 C14 to Locking IEC 60320 C13; 18AWG; 250V 10A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.3in (7.8mm)
- COMPATIBILITY: PC Power Cord IEC 60320 C14 works with North American PDUs and cables; IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more; Replacement PC power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C14 to C13 power cord is available in other lengths

Warranty	Lifetime	
Number of Conductors	3	
Connector Plating	Nickel	
Cable Jacket Material	PVC	
Fire Rating	VW-1 Rated	
Cable Type	SJT	
Maximum Cable Length	4.0 ft [1.2 m]	
	Connector Plating Cable Jacket Material Fire Rating Cable Type	Number of Conductors 3 Connector Plating Nickel Cable Jacket Material PVC Fire Rating VW-1 Rated Cable Type SJT





Connector A 1 - IEC 60320 C14 Power

Connector B 1 - IEC 60320 C13 Power

Power

Input Voltage 250V AC

Input Current 10A

Environmental

Operating Temperature -20 to 105C (-4 to 221F)

Storage Temperature -20 to 105C (-4 to 221F)

Humidity 0% to 65% RH

Physical Characteristics

Color Black

Wire Gauge 18 AWG

Cable Length 4.0 ft [1.2 m]

Cable OD 0.3 in [7.8 mm]

Product Length 4.0 ft [1.2 m]

Product Width 1.2 in [2.9 cm]

Product Height 0.8 in [2.1 cm]

Weight of Product 0.0 oz [0.0 g]

Packaging Information

Package Length 5.7 in [14.5 cm]

Package Width 11.4 in [29.0 cm]

Package Height 1.2 in [3.0 cm]

Shipping (Package) 5.2 oz [148.0 g]

Weight

What's in the Box

Included in Package 1 - 4ft C14 to Locking C13 Power Extension Cord



*Product appearance and specifications are subject to change without notice.