

4ft (1.2m) Power Extension Cord, PDU Style C14 to Locking C13, PDU Power Cord, 10A 250V, 18AWG, Power Extension Cable, TAA Compliant, UL Listed

Produkt-ID: 87L3-8400-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Locking C13 connector avoids accidental power disconnection
- Extend a monitor, scanner, printer, or PC power cord by an additional 4ft

Merkmale

- AC POWER CORD: 4ft (1.22m) power supply extension cable with IEC 60320 C14 to Locking C13 connector is suitable for workstations or rackmount equipment; Securely connect devices to a PDU or extend a C13 power cable; Indoor use; Rated to carry 250V at 10A
- BUILT FOR PERFORMANCE AND SAFETY: UL Listed; Locking C13 connector prevents accidental disconnection; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- SPECS: 4ft (1.22m); TAA Compliant; IEC 60320 C14 to Locking IEC 60320 C13; 18AWG; 250V 10A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.3in (7.8mm)
- COMPATIBILITY: PC Power Cord IEC 60320 C14 works with North American PDUs and cables; IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more; Replacement PC power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C14 to C13 power cord is available in other lengths

Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 3

Steckverbinderplatten Nickel

Typ der PVC
Kabelummantelung

Feuerwiderstandsklass Klasse VW-1

e

Kabeltyp SJT

Leistung

Max. Kabellänge 4.0 ft [1.2 m]

Steckverbinder

Steckverbinder A 1 - IEC 60320 C14 Strom

Steckverbinder B 1 - IEC 60320 C13 Strom

Strom

Eingangsspannung 250V AC

Eingangsstrom 10A

Umgebungsbedingungen

Betriebstemperatur -20° to 105°C (-4° to 221°F)

Lagertemperatur -20° to 105°C (-4° to 221°F)

Feuchtigkeit 0% to 65% RH

Physische Eigenschaften

Farbe Schwarz

Drahtstärke 18 AWG

Kabellänge 4.0 ft [1.2 m]

Außendurchmesser des Kabels 0.3 in [7.8 mm]

Produktlänge 4.0 ft [1.2 m]

Produktbreite 1.2 in [2.9 cm]

Produkthöhe 0.8 in [2.1 cm]

Produktgewicht 4.9 oz [140.0 g]

Verpackungsinformationen

Paketlänge	7.2 in [18.4 cm]
Paketbreite	2.7 in [6.9 cm]
Pakethöhe	1.7 in [4.3 cm]
Versandgewicht (Verpackung)	5.2 oz [148.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 1,2m Einrastender C13 auf C14 Stromkabel Verlängerung
--------------------	--

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.

