

## USB-C Multiport Adapter with Wireless Presenter Remote

### Product ID: BNDDKTCHVPRS

This convenient bundle combines StarTech.com's and equipped with a laser pointer. You can create a permanent or temporary workstation virtually anywhere you go and deliver professional presentations in any meeting or conference room.

This versatile USB-C multiport adapter for laptops makes it easy to create a mobile workstation when you need it most. It features HDMI and VGA ports, so you can easily connect a 4K HDMI or a standard-definition VGA monitor.

Installation is fast and easy, with native support in most operating systems. Plus, the adapter integrates a Gigabit Ethernet port and an additional USB 3.0 port, so you can access a wired network, or connect an additional USB peripheral to your laptop.

The host laptop USB-C port must support DP Alt Mode.

The presentation remote features a sleek, ergonomic design with a wireless range of 90 feet (27 m) and includes the required batteries and a carrying case. The USB receiver is supported by generic HID drivers, ensuring it will work with virtually any Mac or Windows computer.

With a built-in laser pointer, the presentation remote lets you guide your audience's attention to critical information in your on-screen content. It's perfect for PowerPoint presentations, websites or any other visuals you want to share with an audience.

The BNDDKTCHVPRS bundle is backed by a two-year StarTech.com warranty and free lifetime technical support. Our knowledgeable Technical Advisory Team is multilingual and located at our head office.

## Certifications, Reports and Compatibility

### Applications

- Business Travelers
- Educational Institutions & Educators

### Features

- Docking station bundle includes compact USB-C multiport adapter and wireless professional presentation remote
- USB-C multiport adapter supports a VGA or 4K HDMI display plus Ethernet and 1x USB 3.0 port
- The included wireless presentation remote has a range of up to 90' or 27 m
- Gives business travelers the essential connectivity tools they need to make effective boardroom or conference room presentations on the road

---

### Hardware

Warranty	3 Years
4K Support	Yes
Fast-Charge Port(s)	No
Displays Supported	1
Bus Type	USB-C
Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Backward compatible with USB 2.0 and 1.1
Chipset ID	Cypress - CYPD2122 Cypress - CYUSB3314 STMicroelectronics - STDP2650 Chrontel - CH7517 ASIX - AX88179

---

## Performance

Maximum Data Transfer Rate	5 Gbps (USB 3.0) <br / >2 Gbps (Ethernet; Full-Duplex)
Maximum Analog Resolutions	2048 x 1280p - 30Hz (VGA)
Maximum Digital Resolutions	3840 x 2160p - 30Hz (HDMI) Lower resolutions are also supported.
Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	Yes
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes
General Specifications	Remote Interface: USB Remote Max Distance: 27 m (90 ft.) Remote Wavelength: 650+20 mm

Remote Optical Power: 1mW

Remote Wireless Band: 2.4 GHz

Remote Power: Battery Powered

Remote Humidity: 30%~80% RH

Remote Operating Temperature: 5 to 45 (41F to 113F)

Remote Storage Temperature: 5 to 45 (41F to 113F)

Remote Color: Black

Remote Warranty: 2 Years

---

**Connector(s)**

Connector Type(s)	USB Type-C (24 pin) USB 3.0 (5Gbps)
	HDMI (19 pin)
	VGA (15 pin, High Density D-Sub)
	RJ-45
	USB Type-A (9 pin) USB 3.0 (5 Gbps)

---

**Software**

OS Compatibility	Windows 7, 8, 8.1, 10
	macOS 10.10 to 10.15
	Chrome OS

---

**Special Notes / Requirements**

System and Cable Requirements	Host laptop with an available USB-C port (to ensure full functionality, the laptop's USB-C port must support DP alt mode).
-------------------------------	--

Note	For MacBook host systems using macOS 10.12, version 10.12.6 or later is required to support this product.
------	---

Not all USB-C ports support the full functionality of the USB Type-C standard. Ensure that your laptop USB-C port supports DP alt mode.

Only one video output port can be used at the same time (HDMI or VGA). If two displays are connected, the HDMI port takes priority.

A 4K-capable display is required to achieve 4K x 2K resolution (4K is also known as 4K x 2K).



USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps.

The remote is a class 2 laser product

The USB-C port on your host must support DP Alt mode

---

**Power**

Power Source	USB-Powered
--------------	-------------

---

**Environmental**

Operating Temperature	5C to 35C (41F to 95F)
Storage Temperature	-40C to 70C (-40F to 158F)
Humidity	5~95% RH (Non-condensing)

---

**Physical Characteristics**

Product Length	4.5 in [11.4 cm]
Product Width	2.1 in [54 mm]
Product Height	0.7 in [17 mm]
Weight of Product	6.8 oz [192 g]

---

**Packaging Information**

Package Length	8.8 in [22.3 cm]
Package Width	5.0 in [12.6 cm]
Package Height	1.3 in [34 mm]
Shipping (Package) Weight	11.6 oz [329 g]

---

***\*Product appearance and specifications are subject to change without notice.***

