

Fiber Optic Cable - 10 Gb Aqua - Multimode Duplex 50/125 - LSZH - LC/LC - 5 m

Product ID: A50FBLCLC5



The A50FBLCLC5m 850nm Laser-Optimized Multimode Fiber (LOMMF) Aqua Cord features 50/125 micron fiber for high-speed, high bandwidth data transmissions over 10 Gigabit Ethernet and Fiber Channel networks - the perfect solution for fiber cable runs between multiple backbone switches, hubs and routers as well as higher end networking equipment.

This LC-LC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire – an ideal solution for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

Each Duplex 50/125 (OM3) Multimode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability, and is backed by our lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Use in 10 Gigabit High Speed Network Environments
- Telecommunication/Data communication
- Broadband systems
- Ideal solution for data applications requiring high speed data transmission
- Fiber Connections in Patch Panels, Hubs, Switches, Routers

Features

- Attenuation loss meets or exceeds industry standards
- 2x LC MM male connectors
- Laser-optimized multimode fiber (LOMMF)
- OM3 (50/125) 2000MHz multimode fiber
- Compatible with 850nm VCSEL source
- Molded connectors

Hardware	Warranty	Lifetime
	Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
	Fiber Size	50/125
Performance	Maximum Data Transfer Rate	100Gbps 10Gbps / 40Gbps / 100Gbps
	Cable Rating	OM3
	Fiber Classification	Multi Mode
	Type	850nm
	Wavelength	
Connector(s)	Connector A	Fiber Optic LC Duplex
	Connector B	Fiber Optic LC Duplex
Environmental	Operating Temperature	-20C to 60C (-4F to 140F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	0~90% RH
Physical Characteristics	Color	Aqua
	Cable Length	16.4 ft [5 m]
	Diameter	3mm
	Product Length	16.4 ft [5.0 m]
	Product Width	0.0 in [0.000 mm]
	Product Height	0.0 in [0.000 mm]
	Weight of Product	2.4 oz [67.000 g]
Packaging Information	Package Length	8.7 in [2.2 cm]
	Package Width	7.9 in [2.0 cm]
	Package Height	0.9 in [24.000 mm]
	Shipping (Package) Weight	2.7 oz [76.000 g]

What's in the Box	Included in Package	5m 10Gb Aqua Multimode 50/125 Duplex LSZH Fiber Patch Cable LC - LC
--------------------------	---------------------	---------------------------------------------------------------------

**Product appearance and specifications are subject to change without notice.*

