

Dual Monitor Sit-Stand Desk Converter - 35" Wide Work Surface

Product ID: BNDSTSLGDUAL



The dual monitor sit-stand desk converter helps enhance your productivity and comfort. This ergonomic desk solution includes two products: the spacious sit-stand workstation (ARMSTSLG) and the dual monitor mount (ARMDUAL), supporting two monitors up to 24". The articulating arms offer a wide range of motion for convenient flexibility.

With one touch, switch your position from sitting to standing or vice versa, to keep a balanced level of movement throughout the day. The height-adjustable standing desk workstation features a pneumatic spring that makes it easy to raise or lower your work surface up to 15.7" (400 mm), to suit your height requirements (instead of selecting from pre-determined heights). You can also adjust the tension, to make height adjustments even easier.

The spacious 35" (0.9 m) wide ergonomic workstation supports two monitors up to 24" each, giving you the screen space you need for easier multitasking. The articulating monitor arms offer a wide range of motion on several axes, giving you the freedom to place your displays side by side or spread apart. Tilt, pan, and swivel for optimum viewing. The dual arm also rotates 360 for landscape or portrait viewing.

Simply place the sit-stand desk converter on your existing desk (minimum 26" depth). Then, attach the monitor mount using the grommet hole and included grommet mount hardware.

The BNDSTSLGDUAL is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Create a dual-monitor sit-stand workstation for business, corporate, institutional, or home office use
- Install ergonomic desk solutions while saving cost by utilizing existing desks and work spaces
- Utilize multiple monitors to complete your tasks quicker, without having to flip between windows

Features

- Place the sit-stand workstation on your existing desk to create an ergonomic stand-up desk, with spacious 35" (0.9 m) wide work surface
- Lever-controlled pneumatic spring for easy height adjustment (max. height adjustment range: 15.7")
- Dual monitor mount supports two monitors up to 24" each
- Two articulating arms with wide range of motion (360 rotation at support post and elbow, 180 at shoulder, plus tilt and pan +/- 90)
- Maximum arm extension of 17.5" (445 mm)
- Minimum footprint: 660 mm (26") D x 889 mm (35") W
- High-quality construction, engineered with steel and MDF wood base, tray and work surface
- Straight up and down movement, provides a stable workstation with no fear of tipping

Hardware

Warranty	2 Years
Wallmountable	No
Cable Management	Yes
Articulating	Yes
# of Displays Supported	2
Mounting Options	Grommet Hole Mount
VESA Hole Pattern(s)	75x75 mm 100x100 mm

Performance

General Specifications	Height Adjustment Range of Sit-Stand Workstation: 15.7 in [399 mm]
	Height Adjustment Range of Monitor Arm: up to 12 in [304 mm]
	Weight Capacity of Work Surface: 28.1 lb [12.7 kg]
	Weight Capacity of Work Surface with Dual Monitor Arm: 18.6 lb [8.4 kg]
Weight Capacity of Keyboard Tray	5.1 lb [2.3 kg]



Maximum Display Size	24in
Height Adjustment	Yes
Minimum Height	6.3 in [16 cm]
Maximum Height	22.0 in [56 cm]
Maximum Arm Extension	17.5 in [44.5 cm]
Display Tilt	+90 / - 90
Display Swivel	+90 / - 90
Swivel / Pivot	360 around the support post 180 at the shoulder 360 at the elbow
Display Rotation	360

Special Notes / Requirements

Note	Shipping weight may vary. Refer to shipper for exact value.
------	---

Physical Characteristics

Color	Black
Material	Steel, MDF Wood and Plastic
Keyboard Tray Width	26.8 in [68 cm]
Keyboard Tray Depth	10.4 in [26.5 cm]
Product Length	26.4 in [67 cm]
Product Width	35.0 in [88.9 cm]
Product Height	6.3 in [16 cm]
Weight of Product	49.4 lb [22.4 kg]

Packaging Information

Shipping (Package) Weight	60.8 lb [27.5 kg]
---------------------------	-------------------



****Product appearance and specifications are subject to change without notice.***

