

2ft (60cm) Heavy Duty Extension Cord, C19 to C20 Black Extension Cord, 20A 250V, 12AWG, Heavy Gauge Power Extension Cable, AC Power Cable, TAA Compliant, UL Listed

Produkt-ID: BA16-2200-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Heavy Duty power cord supports high-powered equipment and PDUs
- Extend a server or rackmount equipment power cord by an additional 2ft

Merkmale

- **HEAVY DUTY POWER CORD:** 2ft (60cm) 12AWG heavy gauge power cord with IEC 60320 C19 to C20 connector is suitable for servers or other high-powered equipment; Indoor use; Rated to carry 250V at 20A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 2ft (60cm); TAA Compliant; IEC 60320 C19 to IEC 60320 C20; 12AWG; 250V 20A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.44in (11.2mm)
- **COMPATIBILITY:** IEC 60320 C19 to C20 Power extension cord works with North American PDUs and high-powered devices; Extend a power connection to a UPS, Power Supply/PDU, or high-power device; Replacement heavy duty power cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C19 to C20 power cord is available in other lengths

Allgemein

UPC	065030901482
Warranty	Lifetime

Strom

Eingangsspannung	250V AC
Eingangsstrom	20A

Physische
Eigenschaften &
Umgebung

Farbe	Black
Leiterquerschnitt	12 AWG
Cable Length	24.0 in [609.6 mm]
Kabelaußendurchmesser	0.4 in [11.2 mm]
Product Length	24.0 in [610.0 mm]
Product Width	1.3 in [34.0 mm]
Product Height	1.0 in [26.0 mm]
Weight of Product	6.7 oz [190.0 g]
Betriebstemperatur	-20° to 105°C (-4° to 221°F)
Lagertemperatur	-20° to 105°C (-4° to 221°F)
Luftfeuchtigkeit	0% to 65% RH

Hardware

Anzahl der Leiter	3
Steckverbinder-Kontakt beschichtung	Nickel
Kabelmantelmaterial	PVC
Brandschutzklasse	VW-1 Rated
Kabeltyp	SJT

Verpackung &
Lieferumfang

Im Lieferumfang enthalten	1 - 0,6m C19 auf C20 Hochleistungs-Netzkabel
Package Width	8.0 in [202 mm]
Package Depth	5.6 in [142 mm]
Package Height	1.7 in [44 mm]

Shipping (Package)
Weight 7.1 oz [200 g]

Steckverbinder

Anschluss 1 (Anzahl)	1
Anschluss 1	IEC C20 (250V AC, 16A)
Anschluss 2 (Anzahl)	1
Anschluss 2	IEC C19 (250V AC, 16A)

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.