

2U Rack Mount Cantilever Shelf - 125lbs / 56kg - 18 in. Deep

Product ID: CABSHELFHD



The CABSHELFHD 2U 18in Depth Heavy Duty Fixed Rack Mount Shelf lets you add a high-capacity 2U shelf to virtually any standard 19-inch server rack or cabinet with front mount options. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This high-capacity server rack shelf is constructed using 2.3mm SPCC commercial grade cold-rolled steel, providing the additional strength required to hold up to 56kg (125lbs) of equipment - a perfect solution for storing larger, non-rackmount pieces of equipment, heavy tools or peripherals in your rack or cabinet.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- For use with all 19" wide Server Racks and Cabinets
- Supply additional storage space for heavy, mission critical hardware and non-rack mount equipment

Features

- Fits all standard 19" server racks
- SPCC 2.3mm Cold-rolled steel construction
- Front mount design
- Holds up to 56kg (125lbs)
- 2U Heavy Duty Fixed Rackmount Shelf
- TAA compliant for GSA Schedule purchases

Hardware	Warranty	Lifetime
	Frame Type	Steel
	U Height	2U
	Cable Management	No
	Mounting Options	Front Mount (Front Only)
Performance	Weight Capacity (Stationary)	125.0 lb [56.6 kg]
Physical Characteristics	Color	Black
	Material	Steel
	Rail Thickness	0.1 in [2.3 mm]
	Internal Depth	18.0 in [4.6 cm]
	Product Length	0.0 in [0.000 mm]
	Product Width	0.0 in [0.000 mm]
	Product Height	0.0 in [0.000 mm]
	Weight of Product	11.4 lb [5.2 kg]
Packaging Information	Package Length	20.0 in [5.1 cm]
	Package Width	19.8 in [5.0 cm]
	Package Height	4.6 in [1.2 cm]
	Shipping (Package) Weight	13.9 lb [6.3 kg]
What's in the Box	Included in Package	2U High Cap Rack Shelf
	Included in Package	M6 Cage Nuts
	Included in Package	M6 Screws
	Included in Package	Instruction Manual

***Product appearance and specifications are subject to change without notice.**

