

1ft CAT6 Ethernet Cable - Blue CAT 6 Gigabit Ethernet Wire -650MHz 100W PoE RJ45 UTP Molded Network/Patch Cord w/Strain Relief/Fluke Tested/Wiring is UL Certified/TIA

ID del Producto: C6PATCH1BL



The C6PATCH1BL Cat 6 Patch Cable (1 ft) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a durable blue PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat 6 patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Gigabit Patch Cable delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Our Cat6 Ethernet Cables are ETL Verified to meet ANSI/TIA-568.2-D standards, ensuring peak performance for high-speed 10G applications. Independent testing confirms compliance with strict insertion loss, return loss, and crosstalk limits, maintaining stable signal transmission over longer

runs. The STP shielding is verified for EMI resistance, for guaranteed reliability in demanding environments.

Certificaciones, Reportes y Compatibilidad



Aplicaciones

- Diseñado para utilizar con redes Gigabit
- Conecta un hub a un panel de distribución
- Conecta una estación de trabajo a una placa de pared

Características

- Certificación ETL
- Conectores RJ45 moldeados
- Cuidadosamente fabricado y probado, para mantener los niveles de diafonía (Near End Crosstalk) en límites aceptables
- Cubiertas de colores para ayudar a codificarlo por color de sección o departamento
- Fabricado con componentes de la más alta calidad
- Alambre de cobre alta calidad con 24AWG

Hardware

Política de Garantía	Lifetime
Cantidad de Conductores	4 Pair UTP
Cable Tipo Jacket	PVC - Polyvinyl Chloride
Grado de Inflamabilidad	Clasificación CMG (uso general)
Tipo de Cable	Moldeado

Estándar de Cableado TIA/EIA-568-B.1-2001 T568B

Rendimiento

Certificación ETL	Sí
Clasificación de Cables	CAT6 - 650 MHz

Conector(es)

Conector A	1 - RJ-45
Conector B	1 - RJ-45

Características Físicas

Color	Azul
Calibre del Conductor	24 AWG
Tipo de conductor	Cobre trenzado
Longitud del Cable	1.0 ft [0.3 m]
Longitud del Producto	1.0 ft [0.3 m]
Ancho del Producto	0.0 in [0.0 cm]
Altura del Producto	0.0 in [0.0 cm]
Peso del Producto	0.8 oz [23.0 g]

Información de la Caja

Cantidad de Paquetes	1
Longitud de la Caja	5.0 in [12.6 cm]
Ancho de la Caja	7.7 in [19.6 cm]
Altura de la Caja	0.6 in [1.5 cm]
Peso (de la Caja) del Envío	1.1 oz [30.0 g]

Contenido de la Caja

Incluido en la Caja

1 - Cable de Conexión Cat6 de 30cm - Azul

Información Acerca
de la Garantía

Warranty

De Por Vida

* La apariencia y las especificaciones del producto están sujetas a cambios sin previo aviso.