

50ft CAT6 Ethernet Cable - Gray CAT 6 Gigabit Ethernet Wire -650MHz 100W PoE RJ45 UTP Molded Network/Patch Cord w/Strain Relief/Fluke Tested/Wiring is UL Certified/TIA

Nº de produit: C6PATCH50GR



The C6PATCH50GR Cat 6 Patch Cable (50 ft) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a durable gray PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat 6 patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Gigabit Patch Cable delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Our Cat6 Ethernet Cables are ETL Verified to meet ANSI/TIA-568.2-D standards, ensuring peak performance for high-speed 10G applications. Independent testing confirms compliance with strict insertion loss, return loss, and crosstalk limits, maintaining stable signal transmission over longer

runs. The STP shielding is verified for EMI resistance, for guaranteed reliability in demanding environments.

Certifications, rapports et compatibilité



Applications

- Designed for use with Gigabit networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet
- Extend the reach of your Gigabit network devices by 50 ft

Spécifications techniques

- ETL Verified
- HIGH PERFORMANCE CAT6 ETHERNET CABLE: 100% copper for error-free Multi Gigabit 1/2.5/5Gbps connections; 10Gbps up to 160'; Fluke patch cord tested to comply w/ANSI/TIA-568-2.D Category 6; ETL Verified to meet ANSI/TIA-568.2-D standards
- POE SUPPORT: 24 AWG stranded copper conductors & UL Rated Wiring (E132276-A) supports up to 100W for PoE devices like VOIP phone & security systems; IEEE 802.3bt & DTE power compliance reduces cable heating
- QUALITY CONSTRUCTION: ETL & UL certified wire; 50-micron gold-plated connectors prevent rust/corrosion to avoid costly network downtime; High quality PVC jacket resists bending or fraying damage
- EASY INSTALLATION: 50 foot molded patch cord is easy to connect into high density panels with many cables; Compatible w/Cat5e; Available w/Snagless boots for easy wiring conduit installation
- SPECS: Length: 50ft (15.2m) | Color: Gray | 650 MHz Rated | Structure: 4 Pair UTP | RJ45 | Jacket: PVC | Wire Gauge: 24 AWG Copper | Wiring: ANSI/T568B | ETL Verified | Warranty: Lifetime

Matériel

Politique de garantie Lifetime

	Nombre de conducteurs	4 pair UTP
	Type de gaine de câble	PVC - Polyvinyl Chloride
	Résistance au feu	Homologué CMG (usage général)
	Type de câble	Moulé
	Norme de câblage	TIA/EIA-568-B.1-2001 T568B
Performance	Vérifié ETL	Oui
	Calibre du câble	CAT6 - 650 MHz
Connecteur(s)	Connecteur A	1 - RJ-45
	Connecteur B	1 - RJ-45
Caractéristiques physiques	Couleur	Gris
	Calibre du fil	24 AWG
	Type de conducteur	Cuivre torsadé
	Longueur de câble	50.0 ft [15.2 m]
	Longueur du produit	50.0 ft [15.2 m]
	Poids du produit	21.7 oz [616 g]
Informations d'emballage	Quantité par paquet	1
	Longueur du Paquet	9.4 in [23.9 cm]
	Largeur du Paquet	8.9 in [22.5 cm]
	Hauteur du Paquet	2.0 in [5.2 cm]
	Poids brut	1.6 lb [0.7 kg]

Contenu du paquet

Inclus dans le paquet 1 - Câble Patch Moulé Cat 6 de 15,2 m - Gris

Informations de
garantie

Warranty

À Vie

* L'apparence et les spécifications du produit peuvent être modifiées sans préavis