

2U Vented Server Rack Shelf, 12" (31.5cm) Mounting Depth, Cantilever Tray For 19" Rack/Cabinet, Heavy-Duty Steel, Up To 25lb/11.3kg, Includes Cage Nuts/Screws

Product ID: CABSHELFV2U-12-RACK



This 2U vented rack shelf adds 12.4" (31.5 cm) of mounting depth to any EIA-310-compliant 19-inch rack or cabinet. The vented design helps to improve airflow and maintain optimal temperatures for the mounted equipment. The cantilever tray includes cage nuts and screws for quick deployment.

The fixed-rack shelf is made of 14-gauge (1.8mm) SPCC steel for long-term durability and sturdiness while supporting up to 25lb (11.3kg) of equipment. Accommodate server rack equipment, accessories, or non-mountable devices for ease of access and connectivity.

The large venting holes on the shelf surface enable improved airflow to dissipate heat and helps maintain optimal equipment temperatures.

Certifications, Reports and Compatibility

Applications

Features

- **UNIVERSAL 19" FIT:** 2U vented rack-mount shelf is designed to fit EIA-310-compliant 19-inch server racks or cabinets; Mounting depth of 12.4 inches (31.5cm) for data, IT, networking, or non-rack mountable equipment
- **MAXIMIZE VENTILATION:** The venting holes help promote passive airflow for optimal heat dissipation, maintaining consistent temperatures for the mounted equipment
- **STURDY & RELIABLE:** Made from 14-gauge SPCC cold-rolled steel, this front-mounted shelf supports up to 25lb

(11.3kg) and was rigorously stress-tested at 2x the rated capacity, ensuring strength & durability you can count on

- **VERSATILE FUNCTIONALITY:** Organize non-rackmount devices like routers, modems, UPS systems, or other peripherals and tools in a 19" rack in both professional and personal environments; Ideal for home theaters, sound recording studios, AV setups, and more

- **EASY TO INSTALL:** Designed to fit in 2 and 4-post server racks; All hardware provided for quick and easy installation

General

UPC	065030912020
Warranty	Lifetime

Physical & Environmental

Color	Black
Construction Material	Steel
Product Length	19.0 in [48.3 cm]
Product Width	12.6 in [32 cm]
Product Height	3.5 in [88 mm]
Weight of Product	6.0 lb [2.7 kg]

Performance

Weight Capacity of Work Surface	24.9 lb [11.3 kg]
Air Flow Rate	Vented

Hardware

Wallmountable	No
Frame Type	Steel
U Height	2U
Cable Management	No
Tools Included	No
Industry Standards	EIA/ECA-310-E
Mounting Surface Thickness	1.8mm (0.07in)

**Packaging &
In-the-Box**

Included in Package	1 - 2U 2-Post Vented Shelf
	4 - M5 Screws
	4 - M5 Cage Nuts
	1 - Quick-Start Guide
Flat Pack (Assembly Required)	Yes
Package Width	15.8 in [40.1 cm]
Package Depth	22.6 in [57.4 cm]
Package Height	7.5 in [19 cm]
Shipping (Package) Weight	8.0 lb [3.6 kg]

****Product appearance and specifications are subject to change without notice.***